

SNC-UNI

Indoor fixed camera housing



Overview

13-inch indoor aluminium housing with clear window and hinged opening

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Features

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

Supports a variety of cameras

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

Related products



SNC- VB635

Fix-Kamera mit
1.080p/60 Bildern/s,
1/2" Exmor™ CMOS-
Sensor und IPELA
ENGINE EX™ – V-Serie



SNC- VB630

Fix-Kamera mit
1.080p/60 Bildern/s
und IPELA ENGINE
EX™ – V-Serie



SNC- VB600

Fix-Kamera mit
720p/60 Bildern/s und
IPELA ENGINE EX™ –
V-Serie

SNC- EB600

Fix-Kamera mit
720p/30 Bildern/s und
IPELA ENGINE EX™ –
E-Serie

SNC- EB630

Fix-Kamera mit
1.080p/30 Bildern/s
und IPELA ENGINE
EX™ – E-Serie

SNC- EB520

Fix-SD-
Netzwerkkamera
(SVGA) für den
Innenbereich

Gallery

