

SNC-UNIHB

Outdoor fixed camera housing



Overview

13- inch outdoor aluminium housing with clear window and hinged opening

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5- inches in diameter.

Features

Flexible positioning

Designed for mounting to a flat wall or round pole, larger than 3.5- inches in diameter.

All-weather operation

The unit includes a AC 24V heater and blower.

Supports a variety of cameras

Network cameras accepted: Sony's SNC-CH120/CH140/CH220/CH240 cameras. Maximum camera/lens length should not exceed 9.5 inches.

Related products



SNC- VB635

Fix-Kamera mit 1.080p/60 Bildern/s, 1/2" Exmor™ CMOS-Sensor und IPELA ENGINE EX™ – V-Serie



SNC- VB630

Fix-Kamera mit 1.080p/60 Bildern/s und IPELA ENGINE EX™ – V-Serie



SNC- VB600

Fix-Kamera mit 720p/60 Bildern/s und IPELA ENGINE EX™ – V-Serie



SNC- EB600

Fix-Kamera mit 720p/30 Bildern/s und IPELA ENGINE EX™ – E-Serie



SNC- EB630

Fix-Kamera mit 1.080p/30 Bildern/s und IPELA ENGINE EX™ – E-Serie



SNC- EB520

Fix-SD-Netzwerkamera (SVGA) für den Innenbereich

Gallery

