

## UNI-INL7T2

Normal pendant camera housing



### Overview

#### **White pendant indoor camera housing tinted dome**

The UNI-INL7T2 is an Indoor Pendant Mount type Housing for SNC-RH124, RS44N, RS46N, RX-Series, RZ25N. Optically correct polycarbonate Tinted lower dome.

No electronics. The user should provide AC 24V feeds to the camera/enclosure.

#### **Anti glare**

7-inch diameter tinted polycarbonate lower dome.

### Features

#### **Pendant**

White trim ring on a dome semi-flash/ pendant ceiling housing.  
1 1/2-inch NPT quick connect coupling.

## Gallery

