

## SNC-UNI

Indoor fixed camera housing



### Overview

#### **13-inch indoor aluminium housing with clear window and hinged opening**

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

### Features

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

#### **Supports a variety of cameras**

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

### Related products



## **SNC- VB635**

Fix-Kamera mit  
1.080p/60 Bildern/s,  
1/2" Exmor™ CMOS-  
Sensor und IPELA  
ENGINE EX™ – V-Serie



## **SNC- VB630**

Fix-Kamera mit  
1.080p/60 Bildern/s  
und IPELA ENGINE  
EX™ – V-Serie



## **SNC- VB600**

Fix-Kamera mit  
720p/60 Bildern/s und  
IPELA ENGINE EX™ –  
V-Serie

## **SNC- EB600**

Fix-Kamera mit  
720p/30 Bildern/s und  
IPELA ENGINE EX™ –  
E-Serie

## **SNC- EB630**

Fix-Kamera mit  
1.080p/30 Bildern/s  
und IPELA ENGINE  
EX™ – E-Serie

## **SNC- EB520**

Fix-SD-  
Netzwerkkamera  
(SVGA) für den  
Innenbereich

## Gallery

