

## CA-TX70

Digital triax adapter for HXC-D70



### Overview

#### **Enables connection via digital triax to HXCU-TX70 Camera Control Unit**

The CA-TX70 digital triax adaptor for the HXC-D70 studio camera allows connection to the HXCU-TX70 digital triax Camera Control Unit (CCU). With the CCU, it is possible to control the HXC-D70 up to a maximum distance 1200 mt. with 14.5mm cable and 600 mt with 8.5mm cable, including the power and signals of Tally, Intercom, Video Return and also Prompter.

#### **Operates with HXCU-TX70**

The CA-TX70 works seamlessly with the HXCU-TX70 digital triax Camera Control Unit (CCU). The HKCU-FP2 optional front control panel can be attached onto the HXCU-TX70.

### Features

#### **Digital triax connection**

The CA-TX70 helps ensure the best picture quality and easy integration of the HXC-D70 using conventional triax infrastructure up to a maximum distance 1200 mt. with 14.5mm cable and 600 mt with 8.5mm cable.

#### **Connection for all signals**

The CA-TX70 provides flexible integration and the possibility to extend the operation with all signals (Tally, Intercom, Video Return and Prompter) in full HD.

## Related products



### **CBK-CE01**

50-pin camera interface and digital extender for PMW-400/350/300



### **HKC-LC01**

Optical fibre transmission connector



### **CCFN-25**

25 metre optical fibre hybrid cable with opticalCON connector



### **CCFN-50**

50 metre optical fibre hybrid cable with opticalCON connector



### **CCFN-100**

100 metre optical fibre hybrid cable with opticalCON connector



### **HXC-FB80**

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera

## Gallery

