

LA-EB1

B4 lens mount adaptor for FX9,
FS7 and FS7II



Overview

The LA-EB1 Mount Adaptor allows direct attachment of B4 lenses to Sony's PXW-FX9, PXW-FS7 and PXW-FS7M2 XDCAM camcorders. This enables camera operators to use B4 lenses for shooting at high zoom ratios with a deep depth of field (DoF), as typically required for news production applications.

Features

Use B4 lenses with FX9*, FS7 and FS7 II

The LA-EB1 mount adaptor allows attachment of B4 lenses, enabling shooting with a deep DoF at high zoom ratio. With the adaptor fitted, an F drop as small as 0.6 maintains bright images (by using the 2K center scan mode on FS7 and FS7II, S16 2K mode in FX9).

* FX9 requires V3.0 or higher

Quick, easy lens exchange

B4 lenses can be fitted quickly and easily to the FX9, FS7 and FS7II with no tools required.

Clean, low aberration images

ALAC (Auto Lens Aberration Compensation) decreases chromatic aberration when using B4 lenses that support ALAC function.

* Requires DC supply from CBK-FS7BK, XDCA-FS7 or XDCA-FX9

Optimal B4 lens operation

Compatibility with the communication interface of B4 lenses supports news production, just like shoulder-mounted camcorders. Recording Start/Stop can be performed using the lens-mounted REC button, while servo zoom supports one-handed operation. Lens information such as iris and focus can be displayed in the camera viewfinder and saved as metadata for use in post-production.

*Requires DC supply from CBK-FS7BK, XDCA-FS7 or XDCA-FX9

Maximised use of lens assets

The flexibility to use B4 or E-mount lenses with the FX9, FS7 and FS7 II allows broadcasters and rental companies to maximise the use of B4 and E mount lens assets, allowing image capture with both a deep and shallow DoF from a single camera.

Related products



CBK- FS7BK

ENG (Electronic News Gathering) Style
Build-up Kit for FS7
and FS7 II



XDCA-FX9

Extension Unit for FX9
camera

Gallery

