

## PWS-100TD1

### Tape Digitizing Station



#### Overview

#### **Simple-to-use tape digitizing server for efficient migration of legacy videotape archives**

The PWS-100TD1 Tape Digitize Station provides efficient management of the digitization of legacy tape archives – video encoding, tape error checking, file quality control and control of storage are all included. Supporting a number of different codecs, it can create A/V files in your house archive format with proxy's for integration with existing MAM/Archive systems or shelf archive systems with the direct connection of up four Sony Optical Disc Archives (ODS-D77U). Digitization of up to four VTRs can be managed concurrently with the simple user interface provided in the PWS-100TD1.

#### **Efficient digitization of legacy video tape**

Transfer up to four video tapes at a time with error checking

#### **Simple-to-use one-box solution**

Connect the VTRs, connect the storage, start the work

#### **Customers can choose Direct transfer to Optical Disc Archive or transfer to existing Archive/MAM**

Supports existing MAM/Archive solutions or shelf storage solutions with Sony Optical Disc Archive (ODS-D77U)

#### **Proxy Generation for network preview**

Create proxies as part of the digitization process for reviewing or use in the MAM/Archive system

## Features

### **Simple operator interface**

Users can manage up to four concurrent transfers with simple user interfaces and automated error checking

### **Flexible operation: 2IN/2OUT, 3IN/1OUT, 4IN/0OUT**

Flexible configuration to support manual viewing options

### **High-res HD-SDI/SDI preview**

High-resolution file preview for final verification of image quality

### **Multi codec support – XAVC Intra 100, MPEG2 HD422/420, IMX30/40/50**

Extensive video format support for digitization to house archive format

### **Direct connection to ODS-D77U**

Long-term archive storage supported with Sony ODS-D77U Optical Disc Archive

## Related products



### **XDCAM Consolidation and Recycling**

Simple-to-use solution automates data migration from XDCAM Professional Disc to Optical Disc Archive

### **PWA-RCT1**

Recording Control Software for PWS-4500, HKCU-REC55 and HKCU-REC50



## Gallery

