

## SCA-S30

High quality active outdoor loudspeaker for use with Sony's IP cameras



### Overview

Outdoor loudspeakers can be a key part of a surveillance system providing an immediate response to incidents. They can be used to inform, warn and even deter.

The SCA-S30 is a rugged, IP-rated loudspeaker for installation outdoors. It has a powerful 35 Watt output from its own built-in amplifier for clear, high-quality audio.

Easy to install, with the option of wall or pole mounting, the SCA-S30 is IP66 rated for outdoor use

### Features

#### **Active Speaker**

Self-contained unit includes 35 watt amplifier and loudspeaker. Simple to install and operate - with no need for external amplification.

#### **High quality output**

With a wide frequency response and a high sound output (86dBspl/W), this is a highly effective speaker for outdoor use.

#### **Easy to install**

The one-piece nature of this loudspeaker makes it easy to install, with no need for a separate audio amplifier. The power supply is 24v AC for direct connection with Sony IP cameras. Speaker angle

is set by simply tightening or loosening a set of adjustment bolts.

## Designed for outdoor use

The SCA-S30 is IP66 rated and can work in 0-50C degree temperatures. It is able to withstand wind, vibration and other external stresses. The external loudspeaker housing is made from a high durability material to withstand impacts.

## Related products



### SNC- VB635

Box-type 1080p/60 fps Camera with Half-inch Exmor™ CMOS Sensor Powered by IPELA ENGINE EX™ - V Series



### SNC- VB630

Box-type 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VB600

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM632R

Outdoor IR Ruggedized 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM602R

Outdoor IR Ruggedized 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM631

Vandal-resistant Minidome 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM630

Minidome 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM601

Vandal-resistant Minidome 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM600

Minidome 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series

Series

## Gallery

