

SNC-VM642R

Outdoor ruggedised minidome
Full HD IP Network Camera with
IR (V-Series)



Overview

Tough, round-the-clock surveillance in all weathers, with excellent Full HD quality, high frame rate recording and high sensitivity, plus image stabilisation and Advanced IR technology

This minidome network camera delivers Full HD quality images around the clock – indoors or outside. The vandal- and weather-resistant SNC-VM642R is ideal for a wide range of demanding security, surveillance and monitoring applications, from banks, factories, shopping malls and offices to airports, car parks and transportation systems.

The camera captures crisp, low-noise Full HD images, even in challenging low-light conditions. The sensitive 1/2.8" type Exmor R CMOS image sensor is teamed with XDNR processing, improving low-light performance and achieving the minimum illumination of 0.006 lux (30 IRE) in colour mode. Video can be captured at a high maximum frame rate of 60fps – allowing smoother, more accurate viewing of moving objects such as people or vehicles.

View-DR expands dynamic range for significantly improved imaging in high-contrast and strongly backlit scenes, like sun-drenched offices or car park entrances. Image stabilisation keeps video images crisp and clear, even when the camera is subject to

vibration on a mounting pole or bracket.

The camera can see in conditions of complete darkness, with built-in IR (infrared) illumination that's coupled with Advanced IR technology to capture near and far-away objects without overexposure. The SNC-VM642R can clearly capture objects in total darkness at distances up to 100m (30 IRE) from the camera.

The addition of SD card edge storage allows video/audio data to be recorded directly by the camera when triggered by an alarm event. This provides valuable redundancy in the event of temporary network failure: recording to the network server resumes automatically when normal network connection is restored.

Installation of the SNC-VM642R is simplified by the same familiar user interface, usability and form factor as previous-generation Sony V Series cameras. The totally sealed minidome unit assures dependable operation in challenging indoor and outdoor environments. It's capable of operating in extreme temperatures. The camera's vandal-resistant design meets the IK10 standard (protection against mechanical impact), and is IP66 rated for protection against water and dust.

Features

Built to effortlessly handle tough conditions

The camera's vandal-resistant design meets IK10 standards (protection against mechanical impact). IP66-rated waterproof and dust-tight, the camera is ideal for outdoor surveillance, as well as damp or humid indoor environments where water ingress may be encountered.

See every scene clearly with Full HD image quality

View fine detail in a wide range of everyday video security and surveillance environments, from retail spaces to banks and

schools. The sensitive 1/2.8" type Exmor R CMOS image sensor is teamed with XDNR processing, improving low-light performance and achieving the minimum illumination of 0.006 lux (30 IRE) in colour mode

Capture smooth, fluid movement at 60fps

Video images can be captured at a high frame rate of 60fps, allowing precise analysis when stepping through recorded footage frame by frame. It's ideal for applications like city surveillance where it's essential to see what's happening with split-second accuracy.

Steadier, more stable video footage

The in-built image stabiliser minimises the effects of camera shake – for example when the camera's pole mounted or subject to mechanical vibration. With clearer, more stable video images it's easier to see what's happening in any scene.

Don't miss that crucial moment with Intelligent Motion Detection and Face Detection

In-built motion detection can trigger a range of actions, from storage and transfer of images to sounding of external alarms. False alarms caused by noise, weather and environment noise are minimised by a smart processing algorithm. Human face detection is also supported, allowing rapid indexing of recordings to find events where a face is visible in the scene.

Clear pictures in total darkness with Advanced IR

Built-in IR illuminators assist with clearly capturing objects in total darkness at distances up to 100m (30 IRE) from the camera. View-DR technology ensures that clear black-and-white images can be seen both near and far from the camera without overexposure.

Better pictures, day or night

True D/N (Day/Night) function automatically switches the camera to Day or Night mode, depending on ambient light levels.

Optimum picture quality in any situation

A choice of selectable picture modes optimises camera settings for best picture quality in a wide range of applications and lighting environments.

Recording quality to suit your network

Select CBR (constant bitrate), VBR (variable bitrate) or VBR-with-cap compression modes for optimised recording quality depending on IP network conditions.

Edge recording on SD card for reliable operation

SD card edge storage allows video/audio data to be recorded directly by the camera when triggered by an alarm event. This provides valuable redundancy in the event of temporary network failure: recording to the network server resumes automatically when normal network connection is restored.

Detect in confidence with Edge-based Analytics

Powerful DEPA Advanced video analytics enhances Intelligent Motion Detection with rule-based alarm triggers, providing alerts with object filters like 'passing' and 'intrusion' to further reduce false alarms.

Reduce cabling costs with Power Over Ethernet (PoE)

Power over Ethernet (PoE) allows the camera be powered by the same Ethernet cable that's used for data transfer, reducing installation complexity and costs.

View and control with your smartphone

Remotely view live camera images with your Android or iOS smartphone or tablet. You don't even need to download a special app.

ONVIF (Open Network Video Interface Forum) compliance

Support for ONVIF simplifies interoperability with other network

video devices. The ONVIF (Open Network Video Interface Forum) defines a common protocol for the exchange of information between network video devices, including automatic device discovery and video streaming.

Quick, easy installation

Quick, easy adjustment of focus and zoom settings simplifies installation while reducing maintenance time. Configuration of network settings is made simple with the supplied SNC Easy IP Setup Guide application.

Dependable all-weather operation

The camera can operate reliably over a wide temperature range. Ideal for outdoor use, it is IP66 rated, water-proof and dust-tight.

Specifications

Camera	
Image Sensor	1/2.8-type progressive scan Exmor R CMOS sensor
Number of Effective Pixels	Approx. 2.13 Megapixels
Signal System	NTSC/PAL (switchable)
Sync System	Internal synchronization
Minimum Illumination (50 IRE)	Color: 0.01 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0 lx (IR LED On)
	Color: 0.006 lx (F1.2, View-DR Off, VE

Minimum Illumination (30 IRE)	Off, AGC On, 1/30 s, 30 fps) B/W: 0 lx (IR LED On)
Dynamic Range	Equivalent to 90 dB with View-DR technology
S/N Ratio (Gain 0 dB)	More than 50 dB
Gain	Auto
Shutter Speed	1/1 s to 1/10,000 s
Exposure Control	Exposure compensation, Shutter speed, Iris
White Balance	ATW, ATW-PRO, Fluorescent lamp, Mercury lamp, Sodium vapour lamp, Metal halide lamp, White LED, One push WB, Manual, Indoor, Outdoor
Lens	CS-mount varifocal lens
Easy Zoom	Yes
Zoom Ratio	Optical zoom 3x Digital zoom 4x Total zoom 12x
Easy Focus for Setup	Yes
Horizontal Viewing Angle	105.3° to 35.6°

Vertical Viewing Angle	56.9° to 20.1°
Focal Length	f = 3.0 mm to 9.0 mm
F-Number	F1.2 (Wide) to F2.1 (Tele)
Minimum Object Distance	300 mm
Pan/Tilt/Rotation Angle (manual)	±192° -7° to +75° -99° to +180°
IR Illuminator	Yes Wave length (typical): 850 nm , IR LED: 20 pieces)
IR Working Distance (50 IRE)	60 m 197 ft.
IR Working Distance (30 IRE)	100 m 328 ft.
White-light LED Illuminator	No

Camera Features

Day/Night	True D/N
Day/Night linked with Easy Focus	Yes

e-Flip	Yes
Image Rotate	90°, 270°
Mirroring	Yes
Wide-D	View-DR
Tone Correction	Visibility Enhancer
Noise Reduction	XDNR
Image Stabilizer	Electronic
Picture Mode	Yes
Privacy Masking (number)	20
Privacy Masking (shape)	Quadrangle formed by any four corner points
Privacy Masking (color/effect)	Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic
Edge Storage	Yes
Voice Alert	Yes
Vandal Resistant	IK10
Ingress Protection	IP66
	3 independent positions for

Superimpose Number	characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for a logo mark
--------------------	-----------------------------------------------------------------------------------------------------------

Superimpose Language	English
----------------------	---------

Menu Language	English, Japanese, Chinese (simplified), Chinese (traditional), French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai, Turkish, Polish
---------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Video

Resolution	1920 x 1080, 1280 x 720, 1024 x 576, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 640 x 360, 352 x 288, 320 x 184 (H.264, JPEG)
------------	--------------------------------------------------------------------------------------------------------------------------------

Compression Format	H.264 (High/Main/Baseline Profile), JPEG
--------------------	------------------------------------------

Maximum Frame Rate	H.264: 60 fps (1920 x 1080) JPEG: 60 fps (1280 x 720)
--------------------	----------------------------------------------------------

Bitrate Control Mode	CBR/VBR (selectable)
----------------------	----------------------

Range of Bit Rate	64 Kbps to 32 Mbps
-------------------	--------------------

Setting

Solid PTZ	Yes
e-Varifocal	Yes
Adaptive Rate Control	H.264
Bandwidth Control	JPEG
Multi streaming Capability	Yes (3)
Number of Clients	20

Intelligent Video/Audio Analytics

Analytics Architecture	DEPA Advanced
Intelligent Motion Detection	Yes
Face Detection	Yes
Tamper Alarm	Yes
Scene Analytics	Passing, Intrusion, Left Object Detection, Removed Object Detection

Audio

Compression Format G.711/G.726/AAC (16 kHz, 48 kHz)

System Requirements

Operating System Windows 7 (32/64 bit) Ultimate,
Professional Edition
Windows 8.1 Pro (32/64 bit)
Windows 10 Pro (32/64 bit)

Processor Intel Core i7 2.8 GHz or higher

Memory 2 GB or more

Web Browser Microsoft Internet Explorer Ver.
11.0
Firefox Ver. 50.1 (plug-in free viewer
only)
Google Chrome Ver. 55.0 (plug-in
free viewer only)

SNC toolbox Yes

SNC toolbox mobile Yes

Network

IPv4, TCP, UDP, ARP, ICMP, IGMP*,
HTTP, DHCP, DNS, NTP, RTP/RTCP,
RTSP over TCP, SMTP over HTTP,
IPv6, HTTPS, FTP (client), SNMP

Protocols (v1, v2c, v3), SSL

*SSM (Source Specific Multicast) is supported.

QoS	DSCP
Multicast Streaming Support	Yes
ONVIF Conformance	Profile S, Profile T
Authentication	IEEE802.1X

Interface

Analog Video Output	BNC x1, 1.0 Vp-p, 75 Ω, unbalance, sync negative 700 TV lines (analog video)*2
Analog Monitor Output for Setup	Phono jack x1
Microphone Input	Mini jack (monaural)
Line Input	Mini jack (monaural)
Line Output	Mini jack (monaural) Maximum output level: 1 Vrms

Network Port	10BASE-T/100BASE-TX (RJ-45)
Alarm Input (Sensor Input)	x2, make contact, break contact
Alarm Output	x2, AC 24V/DC 24 V, 1 A (mechanical relay outputs electrically isolated from the camera)
Card Slots	SD x 1
Confirmed SD Card Type	Max. 256GB *3

General

Power Requirements	12 V DC \pm 10% 24 V AC \pm 20%, 50 Hz/60 Hz IEEE802.3at compliant (PoE/PoE+ system)
Power Consumption	Max. 22 W (AC 24 V/DC 12 V) Max. 18 W (IEEE802.3at (PoE+)) Max. 12.8 W (IEEE802.3af(PoE))
	-40°C to +60°C (IR Off, PoE+, AC 24 V, DC 12 V) -40°C to +50°C (IR On, PoE+, AC 24 V, DC 12 V) -10°C to +60°C (IR Off, PoE) -10°C to

Operating Temperature	+50°C (IR On, PoE)
	-40°F to +140°F (IR Off, PoE+, AC 24 V, DC 12 V)
	-40°F to +122°F (IR On, PoE+, AC 24 V, DC 12 V)
	14°F to +140°F (IR Off, PoE) 14°F to 122°F (IR On, PoE)
Cold Start Temperature	-30°C to +60°C (IR Off, PoE+, AC 24 V, DC 12 V)
	-30°C to +50°C (IR On, PoE+, AC 24 V, DC 12 V)
	0°C to +60°C (IR Off, PoE) 0°C to +50°C (IR On, PoE)
	-22°F to +140°F (IR Off, PoE+, AC 24 V, DC 12 V)
Cold Start Temperature	-22°F to +122°F (IR On, PoE+, AC 24 V, DC 12 V)
	32°F to +140°F (IR Off, PoE)
	32°F to 122°F (IR On, PoE)
	Storage Temperature
Operating Humidity	20 % to 90 % (no condensation)
Storage Humidity	20 % to 80 % (no condensation)
Built-in Heater	Yes

Dimensions (W x H x D)*1	<p>φ166 x 128 mm</p> <p>φ6 5/8 inches x 5 1/8 inches</p>
Mass	<p>Approx. 1830 g</p> <p>Approx. 4 lb 0.6 oz</p>
External Material	<p>Upper case: ADC12</p> <p>Lower case: ADC12</p> <p>Dome cover: PC</p> <p>Cap:PC</p>
External Color	<p>Top cover: Munsell 4.4BG 8.4/0.2</p> <p>Lower case: Munsell 4.4BG 8.4/0.2</p> <p>Cap: Munsell 4.4BG 8.4/0.2</p>
Safety Regulations	<p>JATE Technical Standard (LAN)</p> <p>UL2044, IEC60950-1 (CB)</p> <p>VCCI (Class A), FCC (Class A), IC (Class A)</p> <p>Emission: EN55032 (Class A)</p> <p>Immunity: EN55024+ EN50130-4</p> <p>Emission: AS/NZS CISPR32 (Class A)</p> <p>KC</p> <p>EMC-TR</p>
	<p>Bracket (1)</p> <p>Template (1)</p> <p>Wire rope (1)</p> <p>Wrench (1)</p>

Supplied Accessories	Camera unit mounting screws (4) Screw (M4 × 8) (2) Safety Regulations (1) Cable holder (for conduit) (1) LAN cable holder (1) Operating Instructions - Download site Information (1)
----------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Optional Accessories	YT-ICB45 (In-ceiling Bracket) SNCA-WP602(Weather Protector)
----------------------	----------------------------------------------------------------

Notes

*1 The values for dimensions are approximate.

*2 Monitor display ratio 4:3

*3 The maximum number of event recording in the SD card is 4000. It may not use the full capacity of the SD card, depending on the limitation set for the event recording.

Gallery

