

## UNI-WMB3

Wall mount bracket for PTZ dome mount security camera housings



### Overview

Protect people, property and assets with this wall mount bracket that's designed specifically for use with Sony PTZ dome mount security camera housings.

Elegantly designed for quick, simple installation, the UNI-WMB3 includes a built in quick-release coupler that's compatible with Sony camera pendant mount dome housings.

This allows the bracket to be used with a wide range of Sony pan/tilt/zoom cameras, including SNC-RS, RH, RZ, RX, ER/EP series models with housing.

Equally suitable for outdoor or indoor operation, the mounting bracket is ruggedly designed in aluminium, with stainless steel hardware and a durable white powder coat finish.

The tamper-resistant removable top cover simplifies wire management and assists with speedy installation.

The UNI-WMB3 wall mount bracket can be combined with these other accessories:

- SNCA-CA2 and UNI-CMA3 for corner mount applications
- UNI-WMBB1 for pole mount or back box applications
- SNCA-POWERBOX for 24 VAC pole/wall mount

- applications
  - SNCA-PM3 for pole mounting applications

## Features

### Wide compatibility

Wall mount bracket's quick-release coupler is compatible with all Sony VA Series Housing models. This allows the bracket to be used with Sony SNC-RS, RH, RZ, RX, ER/EP series dome housing PTZ cameras.

### Designed for easy installation

The bracket's 'lanyard' design allows the use of both hands during installation. Speedy installation is further assisted by a 3/4 inch (27mm) conduit knockout and tamper-resistant removable top cover for simplified wire management.

### Rugged, weatherproof construction

Robust all-aluminium construction with stainless steel hardware and a durable white powder coat finish.

## Specifications

### Architecture / Engineering Specifications

Size (H x W)	7.64 x 9.67 inches (194.1 x 245.6mm)
--------------	--------------------------------------

Weight	3 lbs. (1.4 kg)
--------	-----------------

Body Construction	Aluminum
-------------------	----------

### Shipping

Weight*	3 lbs. (1.4 kg)
---------	-----------------

Dimensions	10.5 x 8 x 4 inches (267 x 203.2 x 102mm) *Shipping weights are dependent on weight of product and shipping materials
------------	--------------------------------------------------------------------------------------------------------------------------

## Attributes

Body Construction	Aluminum
Environment	Indoor / Outdoor
Mounting Style	Wall
RoHS	Yes
WEEE	Yes

## Supplies Accessories

Fitting	¾ inch
UNI-WMBB1	¾ inch
UNI-WMB3	¾ inch
UNI-CMA1	¾ inch

Related products



## **SNC- EB600**

Box-type 720p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



## **SNC- EB600B**

Basic Box-type  
720p/30 fps Camera  
Powered by IPELA  
ENGINE EX™ - E Series



## **SNC- EB630**

Box-type 1080p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



## **SNC- EB630B**

Basic Box-type  
1080p/30 fps Camera  
Powered by IPELA  
ENGINE EX™ - E Series



## **SNC- VB600**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- EP521**

Standard Definition  
(PAL) PTZ Network  
Camera



## **SNC- EP580**

1080p/30 fps PTZ  
Camera - E Series



## **SNC- ER521**

Standard Definition  
(PAL) Rapid Dome  
Network Camera



## **SNC- ER550**

720p/30 fps Rapid  
Dome Camera - E  
Series



## **SNC- ER580**

1080p/30 fps Rapid  
Dome Camera - E  
Series



## **SNC- ER585**

Outdoor Unitized  
1080p/30 fps Rapid  
Dome Camera - E  
Series

## Gallery

