

## YT-ICB630

In-ceiling bracket designed for use with SNC W Series cameras



### Overview

#### **Secure mounting for use with the SNC-WR600/WR630 rapid dome camera**

YT-ICB630 is used when the body of the camera is embedded in the ceiling, or with gypsum boards and similar, where the material used in the ceiling is too fragile to hold ordinary screws.

#### **Strong in-ceiling bracket**

Mass approx. 900g (2lb 3oz) including cover.

### Features

#### **Install camera on ceiling**

Install the camera on the ceiling with the thickness from 10 mm to 35 mm (13/32 ~1 7/16 inches) inclusive.

#### **Use with optional dome cover**

The YT-ICB630 can be used with YT-LD124C/LD124S dome cover.

## Gallery

