

## AC-DN10

### AC Adaptor/Charger



#### Overview

- Compact and lightweight AC adaptor/charger
- Maximum 100 W DC power supply
- V-mount mechanism for direct attachment to compatible camcorders
- XLR-4-pin output to power other equipment
- Charging capability of Sony V-mount lithium

#### Specifications

##### Generic Specifications

Power requirements: AC 100 V to 240 V

DC output: 16.7 V, 6 A

Operating temperature: 0 to 40 °C (32 to 104 °F)

Mass: 800 g (1 lb 12 oz)

Dimensions (W x H x D): 101 x 160 x 37 mm (4 x 6 3/8 x 1 1/2 inches)

Charging time

BP-GL95: 145 minutes

BP-GL65: 155 minutes

BP-L60S: 155 minutes

Eco-info: Lead-free solder is used for soldering.  
Halogenated flame retardants are not used in the cabinets and the printed wiring boards.

---

## Related products



### **HXC-FB80**

Three 2/3-inch  
Exmor™ CMOS sensor  
HD colour studio  
camera

## Gallery

