

HSCU-300

Compact Camera Control Unit for HSC-300 cameras



Overview

Digital Full HD transmission up to 1800m* using standard triax cable

Equipped with the latest Sony-developed digital transmission technology, the HSCU-300 Camera Control Unit (CCU) can transmit high-resolution pictures between the camera and CCU, supporting most live production applications. The HSCU-300 features flexible interfaces of selectable inputs/outputs between HD-SDI and SD-SDI.

* The maximum cable length depends on the camera system configuration, lens type, and the number of cable connections.

Easy integration of HSC-300 into multi camera operation

The HSCU-300 can connect the HSC-300 camera with the MSU-1000/1500 Master Setup Unit, which enables the HSC-300 to be used as a simple studio system or as part of a large-scale broadcasting system consisting of multiple cameras.

Highly compact design

The 1.5 RU-size CCU creates a standardized 19-inch rack system that is ideal for space-limited production areas.

Features

Digital Full HD transmission up to 1800m* using standard triax cable

The HSCU-300 Camera Control Unit (CCU) offers long cable runs of up to 1800m (5906 feet) via a \varnothing 14.5 mm triax cable between the camera and the CCU.

* The maximum cable length depends on the camera system configuration, lens type, and the number of cable connections.

Highly compact design

The 1.5 RU-size CCU creates a standardized 19-inch rack system that is ideal for space-limited production areas

Easy integration of HSC-300 into multi camera operation

The HSCU-300 can connect the HSC-300 camera with the MSU-1000/1500 Master Setup Unit, which enables the HSC-300 to be used as a simple studio system or as part of a large-scale broadcasting system consisting of multiple cameras.

Multi-system input/output interfaces

The HSCU-300 features flexible interfaces of selectable inputs/outputs between HD-SDI and SD-SDI. Other interfaces include VBS in/out, HD/SD component video output, as well as sync out and mic and prompter inputs.

Built-in up and down converters maximise flexibility

The HSCU-300 includes a built down-converter to SD providing simultaneous HD and SD outputs and a simple up-converter to HD.

Cross-compatibility with HXC-100 cameras

The HSCU-300 also provides compatibility with the HXC-100 camera, increasing the flexibility of the system.

Control with Sony Remote Control Panel

The HSCU-300 can be controlled with RCP-700/900 Series Remote Control panels connected with CCA-5 cable or via LAN.

Specifications

General

Power supply	100 to 240 V AC, 50/60 Hz
Operating temperature	5 °C to 40 °C (41 °F to 104 °F)
Storage temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Mass	8.3 kg (18 lb 5 oz)

Input/output connectors

Camera	Triax (1) Kings type (for UC model) Fischer type (for CE model)
Intercom/Tally/PGM	D-sub 25-pin, female (1) INCOM (PROD/ENG), 4W/RTS/CC, 0 dBu TALLY (R, G) PGM 2 systems, -20/0/+4 dBu
Remote	8pin multi-connector (1)
Trunk	D-sub 9-pin, female (1), RS-422A 1 system
Ethernet	8-pin (1)

Input connectors

AC input	100 to 240 V AC
Serial return input	BNC type (2) HD-SDI: SMPTE 292M, 0.8 Vp-p, 75 Ω, 1.485/1.4835 Gbps bit rate SD-SDI: SMPTE 259M, 270 Mbps bit rate HD-SDI/SD-SDI selectable
VBS return input	BNC type (2) VBS: 1.0 Vp-p, 75 Ω
Reference input	BNC type (2), loop-through HD: SMPTE 274M, tri-level sync, 0.6 Vp-p, 75 Ω SD: Black burst (NTSC: 0.286 Vp-p, 75 Ω; PAL: 0.3 Vp-p, 75 Ω)
Prompter input	BNC type (2), VBS signal, 1.0 Vp-p, 75 Ω, 2 ch
Mic remote	D-sub 15-pin, female (1)

Output connectors

Mic output	XLR 3-pin, male (2), 0/-20 dBu
WF remote	D-sub 15-pin, female (1)
HD-SDI/SD-SDI output	BNC type (2) HD-SDI: SMPTE 292M, 0.8 Vp-p, 75 Ω , 1.485/1.4835 Gbps bit rate SD-SDI: SMPTE 259M, 0.8 Vp-p, 75 Ω , 270 Mbps bit rate HD-SDI/SD-SDI selectable
HD-SDI/SD-SDI monitor output	BNC type (2) HD-SDI: SMPTE 292M, 0.8 Vp-p, 75 Ω , 1.485/1.4835 Gbps bit rate SD-SDI: SMPTE 259M, 0.8 Vp-p, 75 Ω , 270 Mbps bit rate HD-SDI/SD-SDI selectable
Pr/R/R-Y, Y/G/Y, Pb/B/B-Y	HD Component video: Y (100% white): 0.7 Vp- p, Pr/Pb (75% color bar): 0.7 Vp-p, 75 Ω HD RGB video R/G/B (100% white): 0.7 Vp-p, 75 Ω SD Component video: Y (100% white): 0.714 Vp-p, Pr/Pb (75% color bar): 0.756 Vp-p, 75 Ω SD RGB video R/G/B (100% white): 0.7 Vp-p, 75 Ω
VBS OUT	BNC (2), VBS 1.0 Vp-p, 75 Ω
PIX OUT	BNC (1), VBS/R/G/B (VBS 1.0 Vp-p, 75 Ω)
WF OUT	BNC (1), VBS/SEQ/R/G/B (VBS 1.0 Vp-p, 75 Ω)
Sync out	BNC type (1) HD: BTA-S001A, tri-level sync, 0.6 Vp-p, 75 Ω SD: composite sync, 0.3 Vp-p, 75 Ω HD SYNC/SD SYNC selectable
WF mode	4-pin (1)

Supplied accessories

Number plates (1 set)
Operation manual (1)

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.