

22-inch cost-effective, lightweight Full HD high grade LCD monitor for studio and field use



Overview

**Lightweight and slim Full HD (1920 x 1080) LMD-A Series monitor with an excellent cost-performance ratio**

**Stylish lightweight and slim body with industry's widest viewing angle**

**HDR production features**

**4K production features**

**Shopping channels feature**

**Enhanced field application features**

**Graphics applications features**

**Latest camera-linkage functions**

**User presets and password protection**

**2K format display and Dual-Link HD-SDI mode**

**Multiple monitors firmware upgrade utility**

Features

**High Dynamic Range\***

**Lightweight and compact with lower power consumption**

**Optimised low-latency I/P conversion**

**Video input versatility**

**Computer input versatility**

**In-Monitor Display (IMD) function**

**Waveform monitor, vector scope and audio level meter display**

**False colour function\***

**Yoke-mount and Wall-mount capability**

**User-friendly operability and user interface**

**Consistent design with PVM-A Series monitors**

**Camera focus function**

**Time code function**

**On screen Tally**

**Network control function**

**Auto white adjustment\***

**Enhanced Picture & Picture function\***

**2K (2048 x 1080) input and image-slide\***

**Camera/lens metadata display function and on-screen tally\***

**Anamorphic image conversion and Active Format Description (AFD) functions\***

**Flexible area marker\*, Grid Display, two Center Markers and Flip functions**

**Power-on setting\***

**User Presets with password lock and short-cut to function key configuration\***

**Multiple monitors upgrade utility\***





Related products



**PXW-X400**

Three 2/3-inch type Exmor CMOS sensors XDCAM weight-balanced advanced shoulder camcorder with HLG option, improved network connectivity and low power consumption



**PXW-X500**

Three 2/3-inch type PowerHAD FX Full HD CCD sensors XDCAM camcorder with multi-format recordings including XAVC



**PXW-X200**

Three 1/2-type Exmor™ CMOS Full HD sensor XDCAM camcorder with 17x zoom lens and XAVC recordings



**HXC-D70H**

Affordable three 2/3-inch Exmor CMOS sensors SD / HD Studio Camera



**NEX-FS700R**

4K Super 35mm Exmor CMOS sensor NXCAM camcorder with E-Mount lens system and 4K/2K RAW recording options



**NEX-FS700**

4K-ready Super 35mm Exmor CMOS sensor NXCAM camcorder with E-Mount lens system



**PXW-X160**

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and XAVC recordings



**PXW-X320**

Three 1/2-inch type Exmor CMOS sensors XDCAM camcorder with 16x zoom HD lens recording Full HD XAVC 100 Mbps, with wireless options



**HXC-D70L**

Affordable three 2/3-inch Exmor CMOS sensors SD / HD Studio Camera with viewfinder



**PXW-Z100**

1/2.33-inch type Exmor R CMOS sensor 4K compact XDCAM camcorder recording on XAVC format



**NEX-EA50M**

NXCAM Large Format Sensor camcorder with E-mount lens system and SELP18105G zoom lens



**HXC-D70K**

Affordable three 2/3-inch Exmor CMOS sensors SD / HD Studio Camera with viewfinder and lens



**PXW-X180**

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and wireless operations, including XAVC recordings



**HXR-MC2500**

1/4-inch Exmor R CMOS sensor HD / SD AVCHD camcorder



**PXW-FS5M2**

'Grab and shoot' Super35 handheld camcorder with stunning new creative look, 4K 120fps HFR and HDR, α Mount lens system, Variable ND Filter, 4K/2K RAW and XAVC recording



**PDW-680**

Three 2/3-inch type Exmor CMOS sensors XDCAM HD shoulder camcorder recording full HD / SD





### HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



### PXW-Z150

Compact handy camcorder delivers broadcast quality 4K and Full-HD



### MCX-500

Multi-Camera Live Producer



### PMW-300K1

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 14x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps



### PMW-300K2

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 16x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps



### PDW-850

Three 2/3-inch Power HAD FX CCD sensors XDCAM HD422 ultimate Professional Disc camcorder with best picture quality and easy-to-share and archive media



### HXR-NX5R

Three 1/2.8-inch Exmor CMOS sensors Full HD AVCHD / XAVC S camcorder with 40x zoom with Clear Image Zoom and built-in wireless functionality.



### NEX-FS700RH

4K Super 35mm Exmor CMOS sensor NXCAM camcorder with 11x Zoom E-Mount lens and 4K/2K RAW recording options



### HXR-NX200

1.0-type Exmor R™ CMOS Sensor 4K, NXCAM camcorder with all-new default look, 24x zoom (FHD Clear Image Zoom), 3 independent manual lens rings plus XAVC S, AVCHD and DV. (PAL-only)



### PXW-Z750

4K 2/3-type 3-chip CMOS Shoulder-mount Camcorder with global shutter, high sensitivity, 4K/HD simultaneous recording, 120p HFR in HD, 12G-SDI and advanced wireless workflow capabilities

## Gallery

