

## NXL-ME80

LAN/WAN Media Edge Processor



### Specifications

#### General

Power requirements AC 100 V - 240 V 50/60Hz

Power consumption 90W(Max)

Dimensions (W x H x D) 210.0 x 41.7 x 350.0mm (Not including protrusions)  
Approx. (8 17/64 x 1 41/64 x 13 25/32 inch)

Mass Approx. 2.9 kg (102.3 oz)

Operating temperature 5 °C to 40 °C (41 °F to 104 °F)

Storage temperature -20 °C to 60 °C (-4 °F to 140 °F)

Storage humidity Under 90%(No condensation)

#### Inputs/Outputs

Reference input	BNC (2), 75 Ω switch with loop-through output HD tri-level sync or Analog black burst
SDI	microBNC(8), Max Input x8 , Output x8 SMPTE ST424, SMPTE ST292, ST2082-1 (No. 1, 5 only)
NETWORK(CONTROL)	RJ45(2) 1000BASE-T/100BASE-TX
NETWORK(WAN)	SFP(2) 1000BASE-** (by SFP transceiver module) *1
NETWORK(LAN)	SFP28(2) 25GBASE-** (by SFP transceiver module) *2

## Notes

\*1

For information on usable SFP transceiver modules (Nevion SFP-1GE-RJ45 / SFP-TR1-850-SR/SFP-TR1-13T-LR, etc.), please contact your Sony service representative or sales representative.

\*2

For information on available SFP28 modules (OTM-25GSR/OTM-25GLR, etc.), please contact your Sony service representative or sales representative.

---

## Gallery

