

SNCA-ZX104

Hybrid camera receiver allows seamless integration of analogue and IP



Overview

The SNCA-ZX104 Hybrid Camera Receiver allows customers to seamlessly integrate images from four different hybrid cameras, enabling their easy and cost-effective migration towards HD IP video surveillance systems.

The SNCA-ZX104 4 channel receiver offers 4 x BNC camera input and 4 x BNC analogue video output.

Specifications

Camera Connection

| | |
|-----------------------------|---|
| Number of Cameras Supported | 4 |
|-----------------------------|---|

| | |
|---------------------------------------|---------|
| Supported Serial PTZ Control Protocol | Pelco-D |
|---------------------------------------|---------|

System Requirements

| | |
|------------------|--|
| Operating System | Microsoft Windows XP (32 bit) Windows Vista (32 bit) Windows 7 (32 bit/64 bit) |
|------------------|--|

| | |
|-------------|---|
| Web Browser | Microsoft Internet Explorer Ver. 6.0, Ver. 7.0, Ver. 8.0 |
|-------------|---|

Interface

| | |
|-----------------------|--|
| Analogue Video Output | BNC x4 (1.0 Vp-p, 75 Ω , NTSC or PAL) |
|-----------------------|--|

| | |
|-----------|-----------------------|
| SLOC Port | BNC x4 (75 Ω) |
|-----------|-----------------------|

| | |
|--------------|-----------------------------|
| Network Port | 10BASE-T/100BASE-TX (RJ-45) |
|--------------|-----------------------------|

| | |
|------------------|---|
| Serial Interface | RS-485 x1 (I/O port for PTZ camera control) |
|------------------|---|

General

| | |
|--------------------|---|
| Power Requirements | DC 12 V (AC 100 V to AC 240 V, 50/60 Hz for AC adaptor) |
|--------------------|---|

| | |
|-------------------|--|
| Power Consumption | Approx. 12.0 W, Approx. 0.22 A/0.12 A (AC adaptor, AC 100 V to AC 240 V) |
|-------------------|--|

| | |
|-----------------------|--------------------------------|
| Operating Temperature | 0°C to +45°C +32°F to 113°F |
|-----------------------|--------------------------------|

| | |
|---------------------|----------------------------------|
| Storage Temperature | -20°C to +60°C -4°F to +140°F |
|---------------------|----------------------------------|

| | |
|--------------------|------------------------------|
| Operating Humidity | 20% to 80% (no condensation) |
|--------------------|------------------------------|

| | |
|------------------------------|---|
| Storage Humidity | 20% to 80% (no condensation) |
| Dimensions (W x H x D) *1 | 210 mm x 44 mm x 250 mm (without projecting parts) 8 3/8 inches x 1 3/4 inches x 9 7/8 inches (without projecting parts) |
| Mass | Approx. 1.1 kg Approx. 2 lb 7 oz |
| Supplied Accessories | CD-ROM (User's Guide, and supplied programs) (1) Installation Manual (1) B&P warranty booklet (1) AC adaptor (1) Power code I/O port connector (1) |

Notes

Notes

[*1] The values for dimensions are approximate.

Related products



SCA-M30

High quality, ceiling microphone for IP security cameras.



SCA-S30



UNI-OPL7C3

Outdoor Pressurized dome camera housing



SNCA-HRX550/EXT12V

Robust, IP66 rated dome housing for



SNCA- HRX550EXT/W

Outdoor wireless
dome camera housing

Gallery

