

## VPL-DW127

2,600 lumens WXGA Desktop projector



### Overview

#### **Economical desktop projector for office and classroom, offering basic high performance and superior ease of use**

The VPL-DW127 is packed with features optimised for the business and education markets at a reasonable price. The projector is compact and lightweight, with its simple design making it very easy to set up.

Sony 3LCD BrightEra™ panel technology provides bright and colourful projection. Plenty of interfaces allow easy connection, while a choice of Picture Modes optimises viewing with any source – slide presentations, PC documents, pictures or videos. There's a range of smart energy-saving features built in, including auto power saving function. And with a recommended lamp replacement time of 10,000 hours, downtime and maintenance costs are minimised.

### Features

#### **Compact, lightweight and stylish design**

The VPL-DW127 has a compact and lightweight body with a small footprint of approximately 315 x 75 x 230.5 mm (12 13/32 x 2 15/16 x 9 1/16 inches) and a light weight of approximately 2.6 kg (5.8 lb). This compact, lightweight projector is convenient for carrying around a meeting room or classroom.

## **Energy efficient with long-lasting lamp of 10,000 hours**

The lamp driver optimally controls the wattage of the lamp and achieves a long-lasting lamp time of 10,000\* hours. The recommended lamp replacement time is extended by 43%, compared to the previous model.

\*Lamp mode: low, Complies with IEC61947 standard

## **Advanced energy-saving features**

Advanced lamp technology enables robust energy-saving features. For example, greater brightness control in Auto Light Dimming mode saves considerable energy when the projector is left on without being used. During projection, Auto Lamp Mode automatically adjusts light output to suit the projected scene. When you need to mute the picture temporarily, light output can be completely deactivated to minimise energy consumption.

## **High image quality 3LCD BrightEra™ natural and vivid colour images**

Widescreen WXGA (1280 x 800) 16:10 screen resolution, 3LCD BrightEra™ natural and vivid colour images, plus various Picture Modes for optimising image quality, make the projector one of the best in its class. Thanks to the optical system projecting three basic colours constantly, the projector offers excellent light efficiency, ensuring colourful and bright images. Sony's BrightEra™ panels deliver improved panel light resistance, higher resolution, high brightness and increased panel reliability. High colour reproducibility is important especially when using colourful content, such as materials used in classrooms.

## **Various picture modes for optimal picture quality**

The projector has six available picture modes for correct picture quality: Dynamic, Standard, Presentation, Blackboard, Game, and Cinema. With six picture modes and three brightness modes combined, the user can select the most suitable picture/brightness combination according to the picture source

and environment, to create the optimal image.

## **Network presentation (LAN)**

When the projector is installed in a LAN, presentations can be projected from any PC and Mac on the network. A tablet or smartphone can be connected at the same time. You can project jpg, pdf and other supported formats. Up to four users can project PC/Mac images simultaneously, while up to eight users can connect to one projector. For PC/Mac, an application, Projector Station for Network Presentation, is provided. For a tablet/smartphone, an application is provided by Pixelworks, downloaded from the web. For details, please visit: <http://PWPresenter.pixelworks.com>

## **Remote control for iOS device**

Projector Remote is a simple remote control application for Sony's projectors. Networked projectors can be controlled by this remote application. Remote Control allows you to operate the projector with simple and easy-to-read buttons.

## **USB display**

The projector allows you to display pictures and audio\* with one USB cable. You do not need to install any driver for this function. It is a convenient way to connect to the projector when you want to connect easily.

\* There is a time lag in video and audio. When not in simple use, it is recommended to use Line-in or HDMI-in.

## **Input name customisation**

It is possible to customise the input names that appear in the input menu on screen. It allows users to understand clearly what equipment is connected.

## Display system

Display system	3 LCD system
----------------	--------------

## Display device

Size of effective display area	0.59" (15 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	------------------------------------------------------------

Number of pixels	3,072,000 (1280 x 800 x 3) pixels
------------------	-----------------------------------

## Projection lens

Focus	Manual
-------	--------

Zoom - Powered/Manual	Manual
-----------------------	--------

Zoom - Ratio	Approx. x 1.3
--------------	---------------

Throw Ratio	1.36:1 to 1.77:1
-------------	------------------

## Light source

Type	Ultra high pressure mercury lamp
------	----------------------------------

Wattage	210 W type
---------	------------

## Recommended lamp replacement time \*1

Lamp mode: High	3000 H
-----------------	--------

---

Lamp mode: Standard    5000 H

---

Lamp mode: Low            10000 H

---

## Filter cleaning / replacement cycle (Max.) \*1

Filter cleaning /  
replacement cycle        1000 H (cleaning)  
(Max.)

---

## Screen size

Screen size                    30" to 300" (0.76 m to 7.62 m)  
(measured diagonally)

---

## Light output

Lamp mode: High            2600 lm

---

Lamp mode: Standard      1900 lm

---

Lamp mode: Low             1500 lm

---

## Color light output

Lamp mode: High            2600 lm

---

Lamp mode: Standard      1900 lm

---

Lamp mode: Low             1500 lm

---

## Contrast ratio (full white / full black) \*2

Contrast ratio (full white / full black)	3000:1
------------------------------------------	--------

## Speaker

Speaker	1 W x 1 (monaural)
---------	--------------------

## Displayable scanning frequency

Horizontal	19 kHz to 92 kHz
------------	------------------

Vertical	48 Hz to 92 Hz
----------	----------------

## Display resolution

Computer signal input	Maximum display resolution: UXGA 1600 x 1200 dots*3
-----------------------	-----------------------------------------------------

Video signal input	NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, 1080/60p, The following items are available for digital signal (HDMI input) only. 1080/60p, 1080/50p
--------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

## Color system

---

Color system	NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N
--------------	----------------------------------------------

---

## Key stone correction (Max)

Vertical	+/- 30 degrees
----------	----------------

---

## OSD language

OSD language	24languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Polish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Vietnamese, Arabic, Farsi, Finnish, Indonesian, Hungarian, Greek)
--------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

---

## INPUT OUTPUT (Computer/Video/Control)

INPUT A	RGB / Y PB PR input connector: Mini D-sub 15-pin (female) Audio input connector: Stereo mini jack (shared with VIDEO IN)
---------	-----------------------------------------------------------------------------------------------------------------------------

---

INPUT B	HDMI input connector: HDMI 19-pin, HDCP support
---------	-------------------------------------------------

---

	Video input connector: Pin jack
--	---------------------------------

---

VIDEO IN	Audio input connector: Shared with INPUT A
----------	--------------------------------------------

LAN	RJ-45, 10BASE-T/100BASE-TX
-----	----------------------------

USB	Type-A
-----	--------

USB	Type-B
-----	--------

## Acoustic noise

Lamp mode: Low	< 35 dB
----------------	---------

## Operating temperature / Operating humidity

Operating temperature / Operating humidity	0°C to 35°C (32°F to 95°F) / 20% to 80% (no condensation)
--------------------------------------------	-----------------------------------------------------------

## Storage temperature / Storage humidity

Storage temperature / Storage humidity	-10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)
----------------------------------------	----------------------------------------------------------------

## Power requirements

Power requirements	AC 100 V to 240 V, 3.0 A to 1.2 A, 50 Hz / 60 Hz
--------------------	--------------------------------------------------



## Power consumption

AC 100 V to 120 V	Lamp mode: High 301 W
-------------------	-----------------------

AC 220 V to 240 V	Lamp mode: High 287 W
-------------------	-----------------------

## Power Consumption (Standby Mode)

AC 100 V to 120 V	0.5 W (when "Standby mode" is set to "Low")
-------------------	---------------------------------------------

AC 220 V to 240 V	0.5 W (when "Standby mode" is set to "Low")
-------------------	---------------------------------------------

## Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	5.3 W (LAN)
	5.9 W (WLAN)
	6.1 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

AC 220 V to 240 V	5.3 W (LAN)
	5.9 W (WLAN)
	6.1 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard")

## Standby Mode/Network Standby Mode Activated

Standby Mode/Network Standby Mode Activated	after about 10 minutes
---------------------------------------------	------------------------

---

## Wireless Network(s) On/Off Switch

Wireless Network(s) On/Off Switch	<ol style="list-style-type: none"> <li>1) Press the MENU button, then select [Connection/Power]</li> <li>2) [WLAN Settings]</li> <li>3) [WLAN Connection]</li> <li>4) Select On or Off</li> </ol>
-----------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

---

## Heat dissipation

AC 100 V to 120 V	1024 BTU/h
AC 220 V to 240 V	977 BTU/h

---

## Dimensions (W x H x D)

Dimensions (W x H x D) (without protrusions)	Approx. 315 x 75 x 230.5 mm (12 13/32 x 2 15/16 x 9 1/16 inches)
----------------------------------------------	------------------------------------------------------------------

---

## Mass

Mass	2.6 kg (5.8 lb)
------	-----------------

## Supplied accessories

Remote commander	RM-PJ8
------------------	--------

Wireless LAN Module	IFU-WLM3
---------------------	----------

## Optional accessories

Replacement lamp	LMP-D213
------------------	----------

Wireless LAN Module	IFU-WLM3
---------------------	----------

## Notes

*1	The figures are the expected maintenance time and not guaranteed. They will depend on the environment or how the projector is used.
----	-------------------------------------------------------------------------------------------------------------------------------------

*2	This value is average.
----	------------------------

*3	Available for the VESA Reduced Blanking signal.
----	-------------------------------------------------

Lamp in this product contains mercury. Disposal of these materials may be regulated due to

Environmental notice  
for customers in the  
USA

environmental considerations. For  
disposal or recycling information,  
please contact your local  
authorities or see  
[www.sony.com/mercury](http://www.sony.com/mercury) for  
additional information.

---

## Gallery

