

CBK-VF02

3.5" Colour LCD HD Viewfinder
for PXW-X500



Overview

3.5" Colour LCD HD Viewfinder for cameras with a rectangle-type 26-pin viewfinder interface. The applicable cameras output the higher resolution QHD signal to this viewfinder. Camera operators can see the LCD, directly, because the optical loupe and the elbow parts can be flipped-up.

3.5" Colour LCD QHD Viewfinder
Uses 26-pin viewfinder interface

Specifications

General

| | |
|--------------|--|
| Power supply | 10.5 to 17.0 V DC (supplied by the camera) |
|--------------|--|

| | |
|-------------------|-------|
| Power consumption | 2.0 W |
|-------------------|-------|

| | |
|-----------------------|-------------------------|
| Operating temperature | 0C to 40C (32F to 104F) |
|-----------------------|-------------------------|

| | |
|---------------------|-------------------------------|
| Storage temperature | -20C to +60C (-4 F to +140 F) |
|---------------------|-------------------------------|

| | |
|------|-----------------------------|
| Mass | Approx. 680 g (1 lb 8.0 oz) |
|------|-----------------------------|

| | |
|---------------------|--|
| External dimensions | 201mm (8 in) x 255mm (10 1/8 in) x 60mm (2 3/8 in) 89mm (3 5/8 in) |
|---------------------|--|

| | |
|--|--|
| 3.5-inch colour TFT transfective LCD Image display area dimensions | 76.8 × 43.2 mm (3 1/8 × 1 3/4 inches) (H/V, 16:9 aspect ratio) |
|--|--|

Performance

| | |
|------------|---|
| Brightness | 200 cd/m ² (typical) (when eyepiece is attached) |
|------------|---|

| | |
|------------|-------------------|
| Resolution | 500 lines or more |
|------------|-------------------|

| | |
|--------------------|------------------|
| Colour temperature | 6500 K (typical) |
|--------------------|------------------|

Connector

| | |
|-----------|------------------------------|
| Connector | Rectangular 26-pin connector |
|-----------|------------------------------|

Supplied accessories

| | |
|----------------------|----------------------|
| Supplied accessories | Operation manual (1) |
|----------------------|----------------------|

Optional accessories

| | |
|----------------------|--|
| Optional accessories | Viewfinder Rotation Assembly : BKW-401 |
|----------------------|--|

Compatible products

Compatible products

PXW-X500, PMW-500, HXC-D70 -
Please note to attach the viewfinder to the PMW-500, the firmware version on the camcorder must be 1.10 or later. To attach the viewfinder to the HXC-D70, the firmware version on the camera must be 1.21 or later.

Notes

Notes

Design and specifications are subject to change without notice.

Related products



BKW-401

Viewfinder Rotation Bracket

Gallery

