

HXC-FB75SC

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD Studio Camera with large viewfinder and 20x zoom lens



Overview

Cost effective system camera ideal for small studio operations, conference events and house of worship applications

Sony introduces an ideal solution for entry level HD & SD live production, delivering better quality and performance for live production.

The HXC-FB75 is a high-performance, yet affordable, HD camera system that inherits Sony's proven field-proven operability from the highly regarded DXC-D Series of system cameras. The camera is equipped with three 2/3-inch Full HD Exmor CMOS sensors to provide excellent sensitivity (F12 at 1080i/60, F13 at 1080i/50) with a low noise ratio for clear images. Those sensors are common to the HXC-P70, HXC-D70 and PXC-X400, and enable perfect integration with those cameras which gives you more flexibility. In addition, a wide range of output formats are available, including 1080i/59.94,50, 1080PsF/29.97,25, 720p/59.94,50, 480i/59.94 and 576i/50. Smooth and precise focusing is enabled by focus assist function and the latest viewfinder options. Video/Audio and control signal transmission, with power, can extend up to 350m via Hybrid Type Optical Fibre Cable. The camera is also controllable from a CCU panel and remote controller.

The HXC-FB75SC camera package is supplied with the HDVF-L750

7-inch full HD colour LCD viewfinder and portable HD 20x zoom lens.

The HXC-FB75SC - enhance your studio production work, cost effectively.

*HXC-FB75KC: [Camera head: viewfinder, mic and lens]

*HXC-FB75SC: [Camera head: large viewfinder and lens]

*HXC-FB75H: [Camera head, only]

Features

Full HD Exmor CMOS sensors

The HXC-FB75 features three 2/3-inch Exmor CMOS sensors to produce excellent HD pictures.

Captures a variety of HD images

The HXC-FB75 produces a variety of selectable progressive and interlace HD signal formats, including 1080i/59.94,50, 1080PsF/29.97,25, 720p/59.94,50

SD down-converter

Down converted SD signal output from HXCU-FB70

Hybrid-type optical fibre cable connection to CCU extends signal transmission with power supply to 350m

Connected to the HXCU-FB70, hybrid type optical fibre cable with a Neutric connector can extend signal transmission with required power supply up to 350m. Full camera control is possible through a user-friendly operational panel designed specifically to work with the HXC series camera.

Long-distance transmission up to 10km with single-mode fibre cable

In the case of connection with a single-mode fibre cable (SMF), transmission can extend up to 10km, if you are using a local power supply. In many facilities the SMF already laid as

infrastructure, it enables you to install the camera system quickly and easily.

HDVF interface for connecting a variety of viewfinders

The HXC-FB75 has an HDVF interface that allows the latest HD portable viewfinders to be used, as well as all types of large HDVF viewfinders.

Wide range of image control functions

The system camera is full of creative image control functions such as MultiMatrix, Skin Tone Detail, Low Key Saturation, Knee Saturation, and Auto Lens Aberration Compensation (ALAC).

Supplied with digital HD large viewfinder and HD lens

The HXC-FB75SC camera package is supplied with the HDVF-L750 7-inch full HD colour LCD viewfinder that offers better and easier operation in studio application. The camera is also supplied with a portable HD 20x zoom lens.

Specifications

General

Power requirements	CCU: DC48V, 2.8A (max.) Ext.DC In: DC12V, 5,4A (max.)
--------------------	--

Power Consumption	Approx.18W (Camera body only) Approx. 31W (Camera body with supplied viewfinder)
-------------------	---

Operating temperature	-10°C to +45°C (14°F to +113°F)
-----------------------	---------------------------------

Storage temperature	-20°C to +60°C (-4°F to +140°F)
Dimensions (W x H x D)*1	160 x 266 x 314 mm (Camera body only) 295 x 455 x 529 mm (Camera body with lens and viewfinder)
Mass	Approx. 3.3 kg (Camera body only) Approx. 6.5 kg (Camera body with lens and viewfinder)

Camera section

Pickup device	3-chip 2/3-inch type CMOS
Effective Picture Elements	1920 x 1080 (H x V)
Signal format	HD: 1080/59.94i, 1080/50i, 1080/29.97PsF, 1080/25PsF, 720/59.94p, 720/50p
Spectrum system	F1.4 prism system
Lens Mount	Sony 2/3"- type bayonet mount
Built-in filters	CC: Electrical
Sensitivity (at 2000 lx, 3200K, 89.9% reflectance)	F12 (59.94 Hz), F13 (50 Hz)

Signal-to-noise Ratio	Typical 60dB*2 (1080/59.94i)
Modulation Depth	HD : 45% or higher at 27.5 MHz (1080i)
Horizontal Resolution	1,000 TV lines or higher
Gain	-3, 0, 3, 6, 9, 12 dB
Shutter Speed	1/100, 1/125, 1/250, 1/500, 1/1000, 1/2000 sec (59.94i mode)
Shutter Speed (Slow Shutter (SLS))	2, 3, 4, 5, 6, 7, 8-frame accumulation (Only for HD1080 mode)

Input/Output

Audio 1 IN/Audio 2 IN	XLR type: 3-pin, female (1 each) MIC IN: -60dBu (Up to -20dBu can be set by using menu or HXCU-FB70), balanced LINE IN: 0dBu, balanced
Intercom	XLR type, 5-pin, female (1)
Earphone	Stereo minijack (1)
DC Input	XLR-type 4-pin (x1), DC 10.5 V to 17 V 4-pin (1), DC 10.5 V to 17 V, 1.5 A

DC Output	(max.)
Prompter/Genlock	BNC (x1); Gen-Lock In or Prompter Out
SDI Input	BNC type (1), for Return
SDI Output	BNC (x1), HD-SDI or SD-SDI selectable
Test Output	TEST Out (Analog output with/without characters), or HD/SD Sync Out
Trunk	TRUNK LINE D-sub 9-pin, female (1) RS-232C
CCU	Optical Fiber (x1), CCFN cable or Single Mode Fiber cable (LC type)
Distance of Power Supply (with HXCU-FB70)	350m (max.)
Distance of Single Mode Fiber Cable (with HXCU-FB70)	10km (max.)
Remote	8pin (x1)
USB	USB 2.0 (x1)

EXT Input/Output	D-Sub 9pin, female (x1)
------------------	-------------------------

Viewfinder	20-pin (1), for HDVF only
------------	---------------------------

Lens	12-pin (x1)
------	-------------

Display (Viewfinder supplied)

Screen Size	155.5 x 87.5 mm (7 inch diagonal)
-------------	-----------------------------------

Aspect Ratio	16:9
--------------	------

Picture Elements	1920(H) x 1080(V) RGB stripe array
------------------	------------------------------------

Lens

Focal Length	8.2mm (11/32 inches) to 164mm (6 1/2 inches)
--------------	--

Zoom	Servo/Manual selectable
------	-------------------------

Zoom Ratio	20 x
------------	------

Maximum Relative Aperture	1: 1.9
---------------------------	--------

Iris	Auto/Manual selectable
------	------------------------

Focus	Full manual focus 900 mm to ∞ (MACRO OFF) 10 mm to ∞ (MACRO ON, Wide)
-------	---

Filter Thread	M82 mm, pitch 0.75 mm
---------------	-----------------------

Macro	On/Off switchable
-------	-------------------

Supplied Accessories

Supplied Accessories	<p>Camera Operation Guide (1) Camera Operation Manual (CD-ROM 1), JP, GB, FR, DE, IT, ES, CS Viewfinder Operation Guide (1) Viewfinder Operation Manual (CD-ROM 1), JP, GB, FR, DE, IT, ES, CS 2/3-inch type HD Portable Lens 7 inch Large Viewfinder (1) Lens Mount Cap (1) Flange back adjustment chart (1) Viewfinder Installation Bracket (1) V-Shoe Bracket (1) Viewfinder Hood (1) Viewfinder Cable 20pin (1) Tally Number Plate (0-9) Camp clamp belt (1)</p>
----------------------	---

Notes

*1	The values for dimensions are approximate.
----	--

The value is in NS (Noise

*2

Suppressor) : ON mode.

Gallery

