

17-inch cost-effective, lightweight basic grade Full HD LCD monitor for versatile use



Overview

Lightweight and slim Full HD (1920 x 1080) LMD-B Series monitor with an excellent cost-performance ratio

Unique SDI and HDMI sync-free side by side configurations*

Industry standard 17-inch screen size and Full HD resolution

Stylish lightweight and slim body

Simple all-in-one design style with front stereo speakers and natural ventilation system

Easy operation in a group of Sony PVM/LMD monitors

Selected essential functions for basic video operations

Features

Unique SDI and HDMI sync-free side by side configurations*

Lightweight and compact with lower power consumption

Optimised low-latency I/P conversion

Video input versatility

Computer input versatility

Waveform monitor, vector scope and audio level meter display

Front stereo speakers

Audio muting *

User-friendly operability and user interface

Consistent design with PVM/LMD-A Series monitors

User reset, key inhibit, user short-cut to function key configuration

Camera focus function

Time code function


Side by side function

On-screen tally

Flip functions

DC low power indicator

Wall-mount capability



Related products



PXW-X400

Three 2/3-inch type Exmor CMOS sensors XDCAM weight-balanced advanced shoulder camcorder with HLG option, improved network connectivity and low power consumption



PXW-X500

Three 2/3-inch type PowerHAD FX Full HD CCD sensors XDCAM camcorder with multi-format recordings including XAVC



NEX-EA50H

NXCAM Large Format Sensor camcorder with E-mount lens system



PXW-FS7M2

4K Super 35mm Exmor CMOS sensor XDCAM camera with Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



PXW-X200

Three 1/2-type Exmor™ CMOS Full HD sensor XDCAM camcorder with 17x zoom lens and XAVC recordings



NEX-FS700R

4K Super 35mm Exmor CMOS sensor NXCAM camcorder with E-Mount lens system and 4K/2K RAW recording options



PXW-X160

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and XAVC recordings



PXW-Z100

1/2.33-inch type Exmor R CMOS sensor 4K compact XDCAM camcorder recording on XAVC format



PXW-X70

1.0 type Exmor R™ CMOS sensor compact XDCAM camcorder with 12x zoom lens recording XAVC, AVCHD and DV



PXW-X180

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and wireless operations, including XAVC recordings



HXR-MC2500

1/4-inch Exmor R CMOS sensor HD / SD AVCHD camcorder



HXR-NX3

Three 1/2.8-inch Exmor CMOS sensors Full HD AVCHD camcorder with 35mm full-frame format equivalent Sony G lens and 40x zoom with Clear Image Zoom



PDW-680

Three 2/3-inch type Exmor CMOS sensors XDCAM HD shoulder camcorder recording full HD / SD



HXR-NX3/1

Three 1/2.8-inch Exmor CMOS sensors Full HD AVCHD camcorder with 35mm full-frame format equivalent Sony G lens and 40x zoom with Clear Image Zoom, with battery pack bundle



HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



PXW-Z450

4K HDR 2/3-type CMOS sensor shoulder camcorder with advanced network features, low power consumption and optimised weight balance



MCX-500

Multi-Camera Live Producer



PXW-Z150

Compact handy camcorder delivers broadcast quality 4K and Full-HD



PMW-300K1

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 14x zoom HD lens system recording XAVC HD 100 Mbps and MPEG



NEX-EA50M

NXCAM Large Format Sensor camcorder with E-mount lens system and SELP18105 G zoom lens

HD422 at 50 Mbps



PMW-300K2

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 16x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps



PXW-FS7

4K Super 35mm Exmor CMOS sensor XDCAM camera with α Mount lens system, 4K/2K RAW and XAVC recording options



PDW-850

Three 2/3-inch Power HAD FX CCD sensors XDCAM HD422 ultimate Professional Disc camcorder with best picture quality and easy-to-share and archive media



PXW-FS5

Grab and Shoot with handheld Super 35



HXR-NX5R

Three 1/2.8-inch Exmor CMOS sensors Full HD AVCHD / XAVC S camcorder with 40x zoom with Clear Image Zoom and built-in wireless functionality.



NEX-FS700RH

4K Super 35mm Exmor CMOS sensor NXCAM camcorder with 11x Zoom E-Mount lens and 4K/2K RAW recording options



HXR-NX200

1.0-type Exmor R™ CMOS Sensor 4K, NXCAM camcorder with all-new default look, 24x zoom (FHD Clear Image Zoom), 3 independent manual lens rings plus XAVC S, AVCHD and DV. (PAL-only)



HXR-NX100

1.0-type Exmor R™ CMOS Sensor NXCAM camcorder with maximum 48x zoom lens and 3 independent manual lens rings recording XAVC S, AVCHD and DV

Gallery

