

## MSU-1500

Master setup unit, multi camera remote control panel for HDC / HSC cameras (vertical type)



### Overview

The MSU-1500 master setup unit is a control panel for camera configuration and maintenance. It is a compact, vertically-oriented device (as opposed to the MSU-1500, which has a larger, horizontally oriented panel), and can control multiple camera systems, using either the CNU-700 Camera Command Network Unit, or using a LAN, in which case up to 96 cameras can be controlled.

**This product contains pre-installed software and requires the purchase of licence keys to activate some functions.**

### Features

#### **Large and flexible system configuration**

The MSU-1500 is part of a family of products that provides flexibility in the configuration of large and small camera control systems.

#### **Ethernet LAN capability**

The MSU-1500 supports inter-connectivity using an Ethernet LAN as well as a CNU-700.

#### **Customisable Switch and menu**

MSU-1500 users can map any function to an assignable switch or menu item

## Specifications

### General

|  |   |
|--|---|
| Power supply                                   | AC 100 - 240 V. 50/60 Hz 0.35 A (Max.)<br>DC 10.5 - 17 V 1.2 A (Max.) |
| Operating temperature                          | 5 °C to 40 °C (41 °F to 104 °F)                                       |
| Dimensions (W x H x D) (excluding protrusions) | 204 × 354 × 67 mm (8 1/8 × 14 × 2 3/4 in.)                            |
| Mass   | Approx. 3.6 kg (7 lb. 15 oz.)   |

### Input/output connectors

|          |                                    |
|----------|------------------------------------|
| Ethernet | RJ-45 8-pin (X1)                   |
| CCU/CNU  | Multi-connector 8-pin, female (x1) |
| AUX      | Multi-connector 8-pin, female (x1) |
| EXT I/O  | D-sub 50-pin, female (x1)          |
| AC IN    | 3-pin (x1)                         |
| DC IN    | 4-pin (x1)                         |

## Related products



### HDC-P43

4K/HD POV Camera



### HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera



### HDC-5500

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



### HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



### HDC-3100

Three 2/3-inch CMOS sensors portable system camera for fibre operation



### HDC-3170

Three 2/3-inch CMOS sensors portable system camera for triax operation



### MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



### MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



### HDC-P31

HD compact POV system camera with enhanced remote features and advanced HDR workflows



### RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



### RCP-3501

Remote-control panel for HDC/HSC/HXC series cameras



### UHC-8300

UHC-8300 8K 3CMOS sensor Camera system includes UHCU-8300 8K Camera Control Unit, UKCU-8001 (8K ST 2110 Interface), UZCU-SNMP80 (SNMP for 8K ST 2110), UKCU-IP01F (Networked Media Interface)

## Gallery

