

Specifications

Dimensions (Approx.)	82.5 x 34 x 174.5mm (W x H x D) Except for the maximum protrusion
Weight (Approx.)	290g (Body only)
Operating temperature	0°C~+40°C
Storage temperature	-20°C~+60°C
Power consumption	0.2W below
Power-supply voltage	4.2~6.0 v ; supplied from Camcorders
Input/Output	CAMERA x3 / 2.5mm TRS Plug REMOTE x1 / 2.5mm TRS Jack OPTION x1 / 3.5mm TRS Jack

Gallery

