

## SRPC-5

### SRMASTER Data Transfer Unit



#### Overview

The SRPC-5 is a cost-effective solution for SRMemory data viewing, logging, and ingesting to off-line editing applications.

The unit offers a web-based GUI, which is used for viewing and ingesting SRMemory content for review on-set and at post-production facilities. It can ingest recorded data to servers and to non-linear editors (NLEs).

In addition, it can duplicate valuable materials from SRMemory to HDCAM SR tape.

#### Features

##### **Fast ingest**

The SRPC-5 allows fast data transfer from SRMemory cards to servers and/or NLEs via an optional 10 GbE network interface. Files and clips can be easily browsed by the SRPC-5 GUI.

It also enables fast ingest from HDCAM SR tapes, at up to twice\* the normal playback speed.

\*Refers to MXF Files.

##### **Simple Viewing**

When material is recorded in SR Video mode, you can browse and view the contents on a broadcast monitor.

## Flawless Tape backup

Content on SRMemory can be duplicated to HDCAM SR tape without any decode/re-encode processes. You can simply duplicate a whole SRMemory card or select individual clips to be perfectly cloned.

## Specifications

### General

Power Requirements 100 to 240 V AC (50/60 Hz)

Power Consumption Approx. 110 W (with all options)

Operating Temperature 5°C to 40°C  
41°F to 104°F

Storage Temperature -20°C to +60°C  
-4°F to +140°F

Mass 10 kg  
22 lb

Dimensions (W x H x D) 427 x 43.6 x 546 mm (excluding protrusion)  
\*1 16 7/8 x 1 3/4 x 21 1/2 inches (excluding protrusion)

### Input/Output

AUX Input BNC (x2)  
Input for uncompressed video data dubbing between SRW-5800

---

AUX Output	A: BNC (x1) B: BNC (x1) HD-SDI (1.485 Gbps) (SMPTE 292M/372M, BTA-S004B standard) 3G-SDI (2.97 Gbps) (SMPTE 424M)
VTR Interface	Local Interface Output A/B: BNC (x2) Local Interface Input A/B: BNC (x2)
Network	RJ-45 jack (x1) 1000BASE-T
Option	PCI Express Slot (x1) (PCI Express x4 Gen1)

---

## On-board Function

---

On-board Function	1D LUT, Down converter, Color space converter
-------------------	---

---

## Confirmed Operational Environment

---

Browser	Firefox, Internet Explorer, Safari, Google Chrome
NFS Server	Redhat Linux E5, Mac OS v10.6
CIFS Server	Windows XP, Windows 7

---

## Supplied Accessories

Supplied Accessories	AC power cord (1)
	Rack mount angle (1) *2
	Washers (4)
	Screws (4)
	SR Viewer (CD-ROM) (1)
	Installation manual (1)
	Operation guide (1)
	Operation manual (1)

## Notes

Note	*1 The values for dimensions are approximate.
	*2 An optional RMM-10 Rack Mount Kit is necessary to mount the unit on a rack.

## Gallery

