

## AC-VQ1051

L series battery AC adapter/charger



### Overview

#### **AC Adaptor / Charger compatible with L series InfoLITHIUM™ batteries**

- Recharging time (Normal / Full charge): F570 110 min / 170 min; F770 185 min / 245 min; F970 285 min / 345 min
- Intelligent display confirms charging time left and remaining battery life in minutes and as percentage
- Relay type recharges up to two batteries simultaneously

### Specifications

#### Basic Specs

Dimension (Approx.)	W 123 x H 53 x D 135mm (4 7/8 x 2 1/8 x 5 3/8 inches)
Weight (Approx.)	400g (14.1oz)
Operating Temperature	+0 to +40°C (+32 to +104°F)
Storage Temperature	-20 to +60°C (-4 to +140°F)

#### AC Power Requirements

Voltage	100-240V
---------	----------

Frequency	50/60Hz
-----------	---------

## DC Power Requirements

Voltage	12/24V
---------	--------

## Power Consumption

Power Consumption	33-43VA (BATT), 40-53VA (VCR/CAMERA)
-------------------	--------------------------------------

## Adapter

Output Voltage in Operating Mode	DC8.4V / 2.0A
----------------------------------	---------------

## Charging Specs

Output Voltage in Charging Mode	DC8.4V / 1.6A
---------------------------------	---------------

Quick Charge	Quick Charge
--------------	--------------

Intelligent Display (LCD)	Y
---------------------------	---

DC Charge	Y
-----------	---

## Charging Time

NP-F970 (Full Charge /  
Normal Charge) 345 min / 285 min

---

NP-F960 (Full Charge /  
Normal Charge) 295 min / 235 min

---

NP-F950 (Full Charge /  
Normal Charge) 260 min / 200 min

---

NP-F930 (Full Charge /  
Normal Charge) 245 min / 185 min

---

NP-F770 (Full Charge /  
Normal Charge) 245 min / 185 min

---

NP-F750 (Full Charge /  
Normal Charge) 205 min / 145 min

---

NP-F730 (Full Charge /  
Normal Charge) 195 min / 135 min

---

NP-F730H (Full Charge  
/ Normal Charge) 205 min / 145 min

---

NP-F570 (Full Charge /  
Normal Charge) 170 min / 110 min

---

NP-F550 (Full Charge /  
Normal Charge) 145 min / 85 min

---

NP-F530 (Full Charge /

---

Normal Charge) 140 min / 80 min

---

NP-F330 (Full Charge /  
Normal Charge) 115 min / 55 min

---

Eco-info (It is indicated from the high order of  
priority)

Use of lead-free solder (use 100% in weight) Lead-free solder is used for soldering

---

Reduction and phase-out of halogenated flame retardant (100%) Halogenated flame retardants are not used in cabinets and in printed wiring boards

---

## Gallery

