

## BC-U1A

Battery charger/AC adaptor for BP-U90/U60/U60T/U30 Lithium-ion battery



### Overview

#### **Charges one BP-U90/U60/U60T/U30 battery**

The BC-U1A battery charger charges one compact BP-U90, BP-U60/U60T, BP-U30 Lithium-ion battery at high speed.

#### **Built-in AC adaptor provides 12 V DC power output**

The BC-U1A also has 12 V DC power output cable to power a camcorder directly.

#### **Compact design for ease of use**

The BC-U1A has a mass of only 340 g (12 oz) and dimensions (W x H x D) of 128 x 45 x 98 mm (5 1/8 x 1 13/16 x 3 7/8 inches).

NOTE: BC-U1A is compliant with safety standard IEC62368-1.

### Specifications

#### General

Power Requirements	AC100V~240V 50/60Hz
--------------------	---------------------

Power consumption	46W
-------------------	-----

DC supply	[36W] 12V / 3.0A
-----------	------------------

Charging Voltage	16.4V
------------------	-------

Dimensions (W x H x D) 128x45x98 (mm)

Mass 340 (g)

Operating [DC supply]-5 °C~+45°C  
Temperature [Charge] 0°C~+45°C

## Approximate charge times

BP-U90 190 minutes

BP-U60 150 minutes

BP-U30 130 minutes

## Supplied Accessories

Supplied Accessories Instruction manual  
Warranty Paper

## Related products



### PXW-FS7M2

4K Super 35mm Exmor CMOS sensor XDCAM camera with Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



### PXW-FS5

Grab and Shoot with handheld Super 35



### PXW-FS5M2

'Grab and shoot' Super35 handheld camcorder with stunning new creative look, 4K 120fps HFR and HDR, α Mount lens system, Variable ND Filter, 4K/2K RAW



### PXW-Z190

4K Handheld Camcorder with all-new 1/3-type 3CMOS with 4K 50p/60p\* recording capability, 25x zoom lens and advanced Face Detection AF

and XAVC recording



## PXW-FS7

4K Super 35mm  
Exmor CMOS sensor  
XDCAM camera with  $\alpha$   
Mount lens system,  
4K/2K RAW and XAVC  
recording options



## MCX-500

Multi-Camera Live  
Producer

## Gallery

