

## BC-U2A

Two-channel simultaneous battery charger/AC adaptor for BP-U90/U60/U60T/U30 Lithium-ion battery



### Overview

#### **Charges two BP-U90/U60/U60T/U30 batteries**

The BC-U2A battery charger can simultaneously charge two compact BP-U90, BP-U60 / 60T or BP-U30 Lithium-ion batteries at high speed

#### **Built-in AC adaptor provides 12 V DC power output while charging one battery**

The BC-U2A also has 12 V DC power output cable to power a camcorder directly, while charging one battery simultaneously.

#### **Portable design for ease of use**

The BC-U2A has a mass of 620 g (1 lb 6 oz) and dimensions (W x H x D) of 177 x 53.2 x 137 mm (7 x 8 1/8 x 5 1/2 inches).

NOTE: BC-U2A is compliant with safety standard IEC62368-1.

### Specifications

#### General

|                    |                     |
|--------------------|---------------------|
| Power Requirements | AC100V~240V 50/60Hz |
|--------------------|---------------------|

|                   |     |
|-------------------|-----|
| Power consumption | 89W |
|-------------------|-----|

|           |                  |
|-----------|------------------|
| DC supply | [36W] 12V / 3.0A |
|-----------|------------------|

|                        |  |
|------------------------|--|
| Charging Voltage       | 16.4V  |
| Dimensions (W x H x D) | 177x53.2x137 (mm)                            |
| Mass                   | 620 (g) +DC out cable                        |
| Operating Temperature  | [DC supply]-5 °C~+45°C<br>[Charge] 0°C~+45°C |

## Approximate charge times

|              |             |
|--------------|-------------|
| BP-U90       | 190 minutes |
| BP-U60 / 60T | 150 minutes |
| BP-U30       | 130 minutes |

## Supplied Accessories

|                      |  |
|----------------------|--|
| Supplied Accessories | Instruction manual<br>Warranty Paper<br>DC out cable |
|----------------------|--|

## Related products



### PXW-FS7M2

4K Super 35mm  
Exmor CMOS sensor  
XDCAM camera with



### PXW-FS5

Grab and Shoot with  
handheld Super 35



### PXW-FS5M2

'Grab and shoot'  
Super35 handheld  
camcorder with



### PXW-Z190

4K Handheld  
Camcorder with all-  
new 1/3-type 3CMOS  
with 4K 50p/60p\*  
recording capability,

Variable ND Filter, E-Mount (Lever Lock), 4K/2K RAW and XAVC recording



## MCX-500

Multi-Camera Live Producer

stunning new creative look, 4K 120fps HFR and HDR,  $\alpha$  Mount lens system, Variable ND Filter, 4K/2K RAW and XAVC recording

25x zoom lens and advanced Face Detection AF

## Gallery

