

## BRAVIA EZ20L Series

Professional display rated for 16/7 operation with essential professional functions; available in a full range of screen sizes



### Overview

#### **Business-friendly with easy content sharing, control and customisation**

Ideal for digital signage and corporate applications, slim, easy-to-use BRAVIA EZ20L Series professional displays add impact to all your visual communications. Very high 4K picture quality is complemented by simple setup, content sharing and networked control in today's connected AV environments.

### Features

#### **Advanced picture technologies for brilliant 4K image quality**

Available in screen sizes from 43"-85", BRAVIA EZ20L Series features advanced Sony picture processing technologies ensure your content looks its best with fine detail, brilliant colours and smooth movement. The panel offers 350 nit brightness\* for high visibility in indoor environments, with a wide viewing angle to ensure everyone in the room enjoys crisp, clear images wherever they're positioned.

\*except 50"/85" (50"/85" are VA panel)

#### **Vivid, natural colour**

Live Color technology brings images alive with a brilliant palette of vibrant, natural colours.

### **Enjoy finer detail**

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution content.

### **Smooth on-screen movement**

Motionflow XR ensures smoother, more natural reproduction of rapidly-moving on-screen images.

### **Great pictures deserve brilliant sound**

The slim design of BRAVIA EZ20L incorporates an X-Balanced Speaker™, offering clear voice quality to enhance video conferences and digital signage.

### **Installation flexibility to suit every environment**

The slim styling of BRAVIA EZ20L Series brings a more professional touch to today's corporate and retail spaces. The display's elegant lines are further enhanced by practical features for seamless integration in any environment.

### **Portrait or landscape installation**

Install BRAVIA in portrait or landscape orientation to suit any corporate space. The display can also be tilted at an angle for even greater flexibility.

NB: FW-85EZ20L installation position cannot be tilted

### **Easy access side-mounted connections**

Signal connections, networking and other interfaces are conveniently side mounted for easy installation and access when the display's in portrait position.

### **Quick, easy setup**

Simple Pro Settings allows customisation of BRAVIA to

suit the demands of any business or retail environment. Schedule power on/off times, select input source on switch on, wake up the display when an input signal's detected – and more.

### **Networked control**

Remotely control and monitor BRAVIA display functions – like power on/off, input source and volume – over IP networks or using familiar RS-232C protocols.

### **Signage made simple**

Built-in support for HTML5 makes it easy to display interactive signage content on BRAVIA without the need for a dedicated set-top box, media player or PC. The on-board BRAVIA Signage Free (BSF) 2.0 app automatically plays out HTML content including videos and photos from the display's internal 16GB storage, or when a USB stick memory is slipped into BRAVIA.

### **Wireless screen mirroring**

Easily mirror content wirelessly from handheld device onto BRAVIA with in-built support for Apple AirPlay and Google Chromecast.

### **Sustainability in every scene**

With growing demand for ever larger display screens, there is also the risk of greater resource and energy use. However, Sony's sustainability commitments are realizing efficiency gains from product development right through to customers viewing screens.

Specifications

General Features

option 1: 85" (US Only)  
option 2: 75"

Screen Size	option 3: 65" option 4: 55" option 5: 50" option 6: 43"
Brightness (cd/m <sup>2</sup> )	350
Contrast Ratio	85": 5000:1 75": 1200:1 65": 1200:1 55": 1200:1 50": 5000:1 43": 1200:1
Dynamic Contrast Ratio	400,000:1
Response Time (ms)	85": 6.5 75": 8.0 65": 8.0 55": 8.0 50": 6.0 43": 8.0
Display resolution (H x V, pixels)	3840 x 2160
HDR (High Dynamic Range) compatibility	Yes (HDR10,HLG)
Aspect Ratio	16:9
Portrait/Tilt Compatibility	Yes

## Display Features

Dimming type	Frame Dimming
Display Device	LCD
Panel Type	85": VA 75": IPS 65": IPS 55": IPS 50": VA 43": IPS
Backlight type	Direct LED
Color gamut (DCI-P3)	85": 92% 75": 75% 65": 75% 55": 75% 50": 75% 43": 75%
Picture Processor	4K Processor X1
Operation time	16 / 7
Deep Black Non-Glare coating	No
Viewing Angle (Right/Left)	178 (89 / 89) degree
Viewing Angle (Up/Down)	178 (89 / 89) degree
<b>Video Specs</b>	
Wide Mode	Auto / Wide zoom / Normal / Full / Full Pixel / Zoom / 14:9
4:3 Default	Yes

Video Processing	4K X-Reality PRO
Motion enhancer	Motionflow XR
HDMI Signal	4096 x 2160p (24, 50, 60 Hz), 3840 x 2160p (24, 25, 30, 50, 60 Hz), 1080p (30, 50, 60 Hz), 1080/24p, 1080i (50, 60 Hz), 720p (30, 50, 60 Hz), 720/24p, 576p, 576i 480p, 480i

## Audio Specs

Speaker Position	Down Firing
Audio Power Output	10W + 10W

## Professional Features

Pro settings	Yes (Simplified)
HDMI auto wake-up	Yes
Operating System	Android TV
On-board Storage (GB)	16GB

## Network Specs

Wi-Fi Certified	Yes
-----------------	-----

Wireless LAN	Integrated
--------------	------------

## Convenience Features

USB playback codecs	MPEG1:MPEG1 / MPEG2 PS:MPEG2 / MPEG2 WEBM:AV1 / AC4 / ogg / AAC
---------------------	---

On Screen Clock	Yes
-----------------	-----

Sleep Timer	Yes
-------------	-----

On/Off Timer	Yes
--------------	-----

Chromecast built-in	Yes
---------------------	-----

Apple AirPlay	Yes
---------------	-----

## Control Specs

IP Control	Yes
------------	-----

RS-232C Control	Yes
-----------------	-----

HDMI-CEC	Yes
----------	-----

## Inputs and outputs

HDCP	HDCP2.3 (for HDMI1 / 2 / 3)
------	-----------------------------

Composite Video Input (s)	1 (Side, Mini jack)
---------------------------	---------------------

HDMI inputs total	3 (3Side)
-------------------	-----------

Analog Audio Input (s) (Total)	1 (Side Analog Conversion)
Digital Audio Output (s)	1 (Side)
USB ports	2 (Side)
Ethernet inputs	1 (Side)
Frame color	85": Black 75": Hairline Black 65": Hairline Black 55": Hairline Black 50": Hairline Black 43": Hairline Black
Stand Design	No Stand
VESA® Hole Spacing Compatible	Yes

## Design Features

VESA® Hole Pitch (W x H)	85": 400 x 400 mm / 15 3/4 x 15 3/4 inch 75": 300 x 300 mm / 11 7/8 x 11 7/8 inch 65": 300 x 300 mm / 11 7/8 x 11 7/8 inch 55": 300 x 300 mm / 11 7/8 x 11 7/8 inch 50": 200 x 200 mm / 7 7/8 x 7 7/8 inch 43": 200 x 200 mm / 7 7/8 x 7 7/8 inch
--------------------------	--



## Accessories

Wall-mount  
adjuster (Bundled)  
\*depending on the  
region. No

Table-top stand  
(Optional)  
\*depending on the  
region. 85": No  
75": No  
65": Yes  
55": Yes  
50": Yes  
43": Yes

Screen Size for  
WEB (diagonal, cm,  
integer or 1st  
decimal) 85": 215cm  
75": 189cm  
65": 164cm  
55": 139cm  
50": 126cm  
43": 108cm

## Environment Specs

Rated Power  
Consumption 85": 248 W  
75": 306 W  
65": 230 W  
55": 202 W  
50": 140 W  
43": 103 W

Power  
Consumption (in  
Standby) 0.5 W

Dynamic Backlight  
Control Yes

Power Saving Mode / Back Light Off Mode Yes

## Measurements

Dimension of TV without Stand (W x H x D)

85": 1901 x 1090 x 73 mm / 74 7/8 x 43 x 2 7/8 inch  
 75": 1686 x 969 x 72 mm / 66 1/2 x 38 1/4 x 2 7/8 inch  
 65": 1462 x 842 x 71 mm / 57 5/8 x 33 1/4 x 2 7/8 inch  
 55": 1243 x 721 x 71 mm / 49 x 28 1/2 x 2 7/8 inch  
 50": 1126 x 653 x 70 mm / 44 3/8 x 25 3/4 x 2 7/8 inch  
 43": 972 x 567 x 70 mm / 38 3/8 x 22 3/8 x 2 7/8 inch

Dimension of TV with Stand (W x H x D)

85": 1901 x 1177 x 456 mm / 74 7/8 x 46 3/8 x 18 inch  
 75": 1686 x 1045 x 410 mm / 66 1/2 x 41 1/4 x 16 1/4 inch  
 65": 1462 x 912 x 338 mm / 57 5/8 x 36 x 13 3/8 inch  
 55": 1243 x 787 x 338 mm / 49 x 31 x 13 3/8 inch  
 50": 1126 x 718 x 286 mm / 44 3/8 x 28 3/8 x 11 3/8 inch  
 43": 972 x 632 x 286 mm / 38 3/8 x 25 x 11 3/8 inch

85": 2035 x 1238 x 237 mm / 80 1/4 x 48 3/4 x 9 3/8 inch  
 75": 1824 x 1114 x 187 mm / 71 7/8 x 43 7/8 x 7 3/8 inch  
 65": 1588 x 965 x 184 mm /

Dimension of Package Carton (W x H x D)	62 5/8 x 38 x 7 1/4 inch 55": 1362 x 840 x 160 mm / 53 5/8 x 33 1/8 x 6 3/8 inch 50": 1240 x 782 x 141 mm / 48 7/8 x 30 7/8 x 5 5/8 inch 43": 1070 x 695 x 141 mm / 42 1/4 x 27 3/8 x 5 5/8 inch
---	--

---

## Weight

Weight of TV without Stand	85": 44.7 kg / 98.5 lb
	75": 30.4 kg / 67 lb
	65": 20.4 kg / 45 lb
	55": 15.3 kg / 33.8 lb
	50": 12.1 kg / 26.7 lb
43": 9.3 kg / 20.5 lb	

---

Weight of TV with Stand	85": 46.2 kg / 101.8 lb
	75": 31.6 kg / 69.7 lb
	65": 21.3 kg / 47 lb
	55": 16.2 kg / 35.7 lb
	50": 12.7 kg / 28 lb
43": 9.8 kg / 21.6 lb	

---

Weight of Package Carton (Gross)	85": 57 kg / 125.6 lb
	75": 45 kg / 99.2 lb
	65": 28 kg / 61.7 lb
	55": 21 kg / 46.3 lb
	50": 16 kg / 35.3 lb
43": 12 kg / 26.5 lb	

---

## Gallery



