

## ECM-678

Shotgun Electret condenser microphone



### Overview

For superior sound quality, choose the ECM-678. It delivers superior sensitivity of -28 dB (0dB=1V/Pa) and extremely low inherent noise of less than 16 dB SPL. This microphone balances the need for a compact size with its ability to deliver excellent performance. The result is a highly directional microphone that is only 250 mm in length.

### Specifications

#### Audio Section

Capsule Type	Mono Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Uni-directional (super-cardioid)
Sensitivity *[1]	-28 dB +/-3 dB
Output Impedance * [2]	200Ω ±20%, Balanced
Dynamic Range	111 dB or more

Signal-to-Noise Ratio    78 dB or more  
\*[3]

Inherent Noise \*[4]    16 dB SPL or less

Induction Noise From  
External Magnetic    0 dB SPL or less  
Field \*[5]

Wind Noise \*[6]    60 dB SPL or less (without screen)

Maximum Input  
Sound Pressure Level    127 dB SPL  
\*[7]

## General Section

Connector    XLR-3-12C (male)

Mic Cable    XLR-3 to XLR-3  
480 mm  
18.9 inches

Power Requirements    External, DC 48 V +/-4 V

Dimensions \*[8]     $\phi$ 20 x 250 mm  
 $\phi$ 13/16 x 9 7/8 inches

Mass    Approx. 7 oz  
Approx. 200 g

Windscreen (1)

## Supplied Accessories

- Stand adaptor (2)
  - Short LR cable (for camcorder use) (1)
  - Operating instructions (1)
  - Mic spacer (2)
  - Mic holder (1)
  - Carrying case (1)
- 

## Notes

### Note

- \*[1] 0 dB = 1 V/Pa, at 1 kHz
  - \*[2] Output impedance at 1 kHz
  - \*[3] A-weighted, 1 kHz, 1 Pa.
  - \*[4] 0 dB SPL = 20  $\mu$ Pa.
  - \*[5] dB SPL/1E-7 T, 0 dB SPL = 20  $\mu$ Pa.
  - \*[6] Wind noise at 2m/s (0 dB SPL = 20  $\mu$ Pa.)
  - \*[7] 0 dB SPL = 20  $\mu$ Pa.
  - \*[8] The values for dimensions are approximate.
- 

## Related products



### **HXC-FB80**

Three 2/3-inch  
Exmor™ CMOS sensor  
HD colour studio

---

camera

## Gallery

