

FW-50EZ20L

50" Professional display rated for 16/7 operation with essential professional functions



Overview

Business-friendly with easy content sharing, control and customisation

Ideal for digital signage and corporate applications, the slim, easy-to-use FW-50EZ20L Professional Display adds impact to all your visual communications. Very high 4K picture quality with 350 nit screen brightness is complemented by simple setup, content sharing and networked control – ideal for today’s connected AV environments.

Features

Brilliant 4K image quality that’s seen by everyone

Advanced Sony picture processing technologies ensure your content looks its best, while 350 nit panel brightness ensures clear visibility in indoor environments.

Enjoy finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution content.

Vivid, natural colour

Live Color technology brings images alive with a brilliant palette of vibrant, natural colours.

Smooth on-screen movement

Motionflow XR ensures smoother, more natural reproduction of rapidly-moving on-screen images.

Great pictures deserve brilliant sound

The slim design of FW-50EZ20L incorporates an X-Balanced Speaker™, offering clear voice quality to enhance video conferences and digital signage.

Portrait or landscape installation

Install BRAVIA in portrait or landscape orientation to suit any corporate space.

Easy access side-mounted connections

Signal connections, networking and other interfaces are conveniently side mounted for easy installation and access when the display's in portrait position.

Quick, easy setup

Simple Pro Settings allows customisation of BRAVIA to suit the demands of any business or retail environment. Schedule power on/off times, select input source on switch on, wake up the display when an input signal's detected – and more.

Networked control

Remotely control and monitor BRAVIA display functions – like power on/off, input source and volume – over IP networks or using familiar RS-232C protocols.

Signage made simple

Built-in support for HTML5 makes it easy to display interactive signage content on BRAVIA without the need for a dedicated set-top box, media player or PC. The on-board BRAVIA Signage Free (BSF) 2.0 app automatically plays out HTML content including videos and photos from the display's internal 16GB storage, or when a USB stick memory is slipped into BRAVIA.

Wireless screen mirroring

Easily mirror content wirelessly from handheld device onto BRAVIA with in-built support for Apple AirPlay and Google Chromecast.

Sustainability in every scene

With growing demand for ever larger display screens, there is also the risk of greater resource and energy use. However, Sony’s sustainability commitments are realizing efficiency gains from product development right through to customers’ viewing screens.

Specifications

General Features	
Screen Size	50"
Brightness (cd/m ²)	350
Contrast Ratio	5000:1
Dynamic Contrast Ratio	400,000:1
Response Time (ms)	6
Display Resolution (H x V, pixels)	3840 x 2160
HDR (High Dynamic Range) Compatibility	Yes (HDR10,HLG,Dolby Vision)
Aspect Ratio	16:09

Portrait/Tilt Compatibility	Yes
--------------------------------	-----

Display Features

Dimming Type	Frame Dimming
--------------	---------------

Display Device	LCD
----------------	-----

Panel Type	VA
------------	----

Backlight Type	Direct LED
----------------	------------

Colour Gamut (DCI-P3)	75%
-----------------------	-----

Picture Processor	4K Processor X1
-------------------	-----------------

Operation Time	16/7
----------------	------

Deep Black Non-Glare Coating	No
---------------------------------	----

Haze (%)	3%
----------	----

Viewing Angle (Right/Left)	178 (89 / 89) degree (CR >10)
-------------------------------	-------------------------------

Viewing Angle (Up/Down)	178 (89 / 89) degree (CR >10)
----------------------------	-------------------------------

Video Specification

Wide Mode	Auto / Wide zoom / Normal / Full / Full Pixel / Zoom / 14:9
-----------	---

4:3 Default	Yes
-------------	-----

Video Processing	4K X-Reality PRO
------------------	------------------

Motion Enhancer	Motionflow XR
-----------------	---------------

HDMI Signal	4096 x 2160p (24, 50, 60 Hz), 3840 x 2160p (24, 25, 30, 50, 60 Hz), 1080p (30, 50, 60 Hz), 1080/24p, 1080i (50, 60 Hz), 720p (30, 50, 60 Hz), 720/24p, 576p, 576i 480p, 480i
-------------	---

Audio Specification

Speaker Position	Down Firing
------------------	-------------

Audio Power Output	10W + 10W
--------------------	-----------

Professional Features

Pro Mode	Yes (Simplified)
----------	------------------

HDMI Auto Wake-Up	Yes
-------------------	-----

Operating System	Android TV
------------------	------------

On-board Storage (GB)	16GB
-----------------------	------

Network Specification

Wi-Fi Certified	Yes
-----------------	-----

Wireless LAN	Integrated
--------------	------------

Convenience Features

USB Playback Codecs	MPEG1:MPEG1 / MPEG2 PS:MPEG2 / MPEG2 WEBM:AV1 / AC4 / ogg / AAC
---------------------	---

On Screen Clock	Yes
-----------------	-----

Sleep Timer	Yes
-------------	-----

On/Off Timer	Yes
--------------	-----

Chromecast Built-In	Yes
---------------------	-----

Apple AirPlay	Yes
---------------	-----

Control Specifications

IP Control	Yes
------------	-----

RS-232C Control	Yes
-----------------	-----

HDMI-CEC	Yes
----------	-----

Inputs and Outputs

HDCP	HDCP2.3 (for HDMI1/2/3/4)
------	---------------------------

Composite Video Input (s)	1 (Side, Mini jack)
---------------------------	---------------------

HDMI Inputs Total	3 (3 Side)
-------------------	------------

Analog Audio Input (s) (Total)	1 (Side Analog Conversion)
--------------------------------	----------------------------

Digital Audio Output (s)	1 (Side)
--------------------------	----------

USB Ports	2 (Side)
-----------	----------

Ethernet Inputs	1 (Side)
-----------------	----------

Design Features

Frame Colour	Hairline Black
--------------	----------------

Stand Design	No Stand
--------------	----------

VESA® Hole Spacing Compatible	Yes
-------------------------------	-----

VESA® Hole Pitch (W x H)	200 x 200 mm / 7 7 / 8 x 7 7 / 8 inch
--------------------------	---------------------------------------

Environment Specifications

Screen Size for WEB (diagonal, cm, integer or 1st decimal)	126 cm
---	--------

Rated Power Consumption	140 W
-------------------------	-------

Power Consumption (in Standby)	0.5 W
--------------------------------	-------

Dynamic Backlight Control	Yes
---------------------------	-----

Power Saving Mode	Yes
-------------------	-----

Measurements

Dimension of TV without Stand (W x H x D)	1126 x 653 x 70 mm / 44 3 / 8 x 25 3 / 4 x 2 7 / 8 inch
---	---

Dimension of TV with Stand (W x H x D)	1126 x 718 x 286 mm / 44 3 / 8 x 28 3 / 8 x 11 3 / 8 inch
--	---

Dimension of Package	1240 x 782 x 141 mm / 48 7 / 8 x 30 7 / 8 inch
----------------------	--

Carton (W x H x D) / 8 x 55 / 8 inch

Weight

Weight of TV without Stand 12.1 kg / 26.7 lb

Weight of TV with Stand 12.7 kg / 28 lb

Weight of Package Carton (Gross) 16 kg / 35.3 lb

Accessories

Table-Top Stand (Optional) Yes (Depending on Region)

Related products



BRAVIA EZ20L Series

Professional display rated for 16/7 operation with essential professional functions; available in a full range of screen sizes

Gallery



