

## HDVF-L10

### 3.5" Colour LCD HD Viewfinder



#### Overview

3.5" Colour LCD HD Viewfinder for cameras with a round-type 20-pin viewfinder interface. The applicable cameras output the higher resolution QHD signal to this viewfinder. Camera operators can see the LCD, directly, because the optical loupe and the elbow parts can be flipped-up.

#### **3.5" Colour LCD QHD Viewfinder**

#### **Uses round-type 20-pin viewfinder interface**

#### **Switchable display mode**

#### Specifications

##### General

|              |  |
|--------------|--|
| Power supply | 10.5 to 17.0 V DC (supplied by the camera) |
|--------------|--|

|                   |       |
|-------------------|-------|
| Power consumption | 3.3 W |
|-------------------|-------|

|                       |             |
|-----------------------|-------------|
| Operating temperature | -5°C - 45°C |
|-----------------------|-------------|

|                     |                               |
|---------------------|-------------------------------|
| Storage temperature | -20C to +60C (-4 F to +140 F) |
|---------------------|-------------------------------|

|                     |  |
|---------------------|--|
| Mass                | 700 g  |
| External dimensions | 201mm (8 in) x 255mm (10 1/8 in) x 60mm (2 3/8 in) 89mm (3 5/8 in) |

|  |  |
|--|--|
| 3.5-inch colour TFT transfective LCD Image display area dimensions | 76.8 × 43.2 mm (3 1/8 × 1 3/4 inches) (H/V, 16:9 aspect ratio) |
|--|--|

## Performance

|                    |   |
|--------------------|---|
| Brightness         | 200 cd/m <sup>2</sup> (typical) (when eyepiece is attached) |
| Resolution         | 500 lines or more   |
| Colour temperature | 6500 K (typical)  |

## Connector

|           |                             |
|-----------|-----------------------------|
| Connector | Round-type 20-pin connector |
|-----------|-----------------------------|

## Supplied accessories

|                      |                      |
|----------------------|----------------------|
| Supplied accessories | Operation manual (1) |
|----------------------|----------------------|

## Optional accessories

Viewfinder Rotation Assembly :

Optional accessories    BKW-401

---

## Compatible products

Compatible products    HXC-FB75KC, HXC-FB75H, HDC-1700, HDC-2400, HDC-2500, HDC-2570, HDC-3300R, HDC-4300, HSC-100R, HSC-100RF, HSC-300R, HSC-300RF, PDW-680, PDW-700, PDW-850, PDW-F800, PMW-500, PXW-X400, PXW-X500

---

## Notes

Notes    Design and specifications are subject to change without notice.

---

## Related products



### **HXC-FB80**

Three 2/3-inch  
Exmor™ CMOS sensor  
HD colour studio  
camera

## Gallery

