

## SZC-4002 / SZC-4002M / SZC-4002W

HFR Upgrade for F65, F55 and HDC-4300



### Overview

The SZC-4002, SZC-4002M and SZC-4002W are the software licenses of HFR Software with the BPU-4000 or BPU-4500 series (including BPU-4500A) Baseband Processor Units.

Installing SZC-4002, SZC-4002M and SZC-4002W on the BPU-4000 or BPU-4500 series (including BPU-4500A) enables High Frame Rate format output, when connected to a PMW-F55 Solid-State Memory Camcorder or F65 Digital Motion Picture Camera or HDC-4300 Color Camera, allowing you to transfer and perform signal processing of HFR images.

The licenses give you a high level of flexibility to purchase the equipment you want, when you want it, with the confidence your baseband processor unit is future-proofed for changing demands.

The SZC-4002 can be permanently used.  
The SZC-4002M can be used for 30 days.  
The SZC-4002W can be used for 7 days.

**Activation key for pre-installed software.**

## Related products



### **PMW-F55**

Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K/4K on SxS memory plus 16-bit RAW 2K/4K output



### **F65**

Super 35mm 8K CMOS sensor SRMASTER camera



### **HDC-4300**

4K/HD System Camera



### **BPU-4500A**

4K/HD baseband processor unit for IP network production



### **BPU-4500**

4K / HD baseband processor unit for IP network



### **BPU-4000**

4K base band processor unit

## Gallery

