

## UNI-OSL7T2

7-inch outdoor vandal-resistant tinted surface-mount housing with heater/blower for SNC-RH124, SNC-RS44/46, SNC-RX, SNC-ER/EP and SNC-ZR/ZP series of PTZ cameras, AC 24V power



### Overview

#### **Outdoor vandal resistant surface-mount enclosure with thermostatically controlled heater/ blower**

The surface-mount 7-inch vandal resistant rugged housing offers versatility and camera protection in a compact size. These outdoor surface mount enclosures can be mounted facing down or facing up toward the sky. The housing is available with a tinted dome. AC 24V input is required for the heater.

#### **Tinted dome**

7-inch polycarbonate.

### Features

#### **Outdoor vandal resistant surface-mount housing**

7-inch tinted polycarbonate lower dome.

#### **Thermostatically controlled heater and blower**

AC 24V input.

## Gallery

