

## URX-P40

UWP-D portable receiver



### Overview

The demand for high quality audio is increasing as high resolution content becomes prevalent in the video production industry. Today's content creators are faced with the challenge of capturing high-quality audio quickly, reliably and with limited resources.

Offering superb sound quality with digital processing, reliable RF transmission, true double tuner diversity reception and friendly features, the UWP-D series is an ideal partner for ENG (electronic news gathering) and EFP (electronic field production), as well as documentaries and weddings.

- High quality sound with Sony digital audio processing
- NFC SYNC function for quick and easy secure channel setting
- True double tuner diversity for stable signal reception
- Channel memory for fast switching between two receiver frequencies
- Headphone output for monitoring
- Monitor mode for using a receiver as an ear monitor
- Compatibility with Sony WL-800/UWP series
- Output level control for receiver
- High visibility OLED display, ideal for indoor/outdoor use
- USB connector for power supply
- Digital audio interface support with SMAD-P5 Multi

## Interface (MI) Shoe Adaptor (option)\*

\* For details on cameras that support this function, visit the Sony website.

## Features

**Digital audio processing for high quality sound**

Advanced digital audio processing technology by Sony assures high quality sound with improved transient response performance. A new [optional] digital audio interface enables direct digital sound recording with many Sony professional camcorders and Alpha interchangeable lens cameras via the SMAD-P5 Multi Interface MI shoe adaptor, bypassing A/D and D/A conversion stages to further ensure excellent sound quality.

**Seamless camcorder integration**

Integration with compatible\* Sony camcorders (requires SMAD-P5 Multi Interface shoe adaptor) displays audio information such as RF level meter, audio mute status and transmitter low battery alert in the camera's viewfinder. Via the SMAD-P5, audio signals are transmitted from receiver to camera without requiring a cable connection. The wireless receiver can also receive power from the camera, with synchronised power on/off between camera and receiver for more effective power management.

\*See details on SMAD-P5 for compatibility information.

**Fast, easy frequency setting**

Sony's uniquely user-friendly NFC SYNC feature allows quick, intuitive secure channel setting between transmitter and receiver.

**Light, compact design**

Reduced system size and weight enable superior mobility in a wide range of applications including news, documentaries,

weddings and remote production. The receiver's compact size and light weight make it an ideal partner for use small camcorders and interchangeable lens digital cameras.

## Specifications

### GENERAL

Oscillator Type	Crystal-controlled PLL synthesizer
-----------------	------------------------------------

Reception Type	True diversity method
----------------	-----------------------

Antenna Type	1/4 $\lambda$ wavelength wire antenna (angle-adjustable)
--------------	--

Carrier Frequencies	<p>14UC : 470.125 MHz to 541.875 MHz(UHF-TV channels 14 to 25)</p> <p>25UC : 536.125 MHz to 607.875 MHz (UHF-TV channels 25 to 36)</p> <p>42LA : 638.125 MHz to 697.875 MHz(UHF-TV channels 42 to 51)</p> <p>90UC : 941.625 MHz to 951.875 MHz, 953.000 MHz to 956.125 MHz, and 956.625 MHz to 959.625 MHz</p> <p>21CE : 470.025 MHz to 542.000 MHz(UHF-TV channels 21 to 29)</p> <p>33CE : 566.025 MHz to 630.000 MHz(UHF-TV channels 33 to 40)</p> <p>42CE : 638.025 MHz to 694.000 MHz (UHF-TV channels 42 to 48)</p> <p>38CN : 710.025 MHz to 782.000 MHz(UHF-TV channels 38 to 46)</p>
---------------------	---

	<p>E : 794.125 MHz to 805.875 MHz</p> <p>BJ: 806.125 MHz to 809.750 MHz</p> <p>KR : 925.125 MHz to 937.500 MHz</p>
Frequency Response	<p>23 Hz to 18 kHz (Typical) (UC, U, CE, LA, CN, E, KR models)</p> <p>40 Hz to 15 kHz (Typical) (J model)</p>
Signal-to-Noise Ratio	60dB (1kHz sine wave, 5kHz modulation)
Distortion (T.H.D)	0.9% or less (1kHz sine wave, 5kHz modulation)
Audio Delay	<p>Approx. 0.35 ms (analog output)</p> <p>Approx. 0.24 ms (digital output)</p>
Audio Output Connector	3.5mm diameter 3-pole locking mini jack, external connection
Audio Output Level	<p>-60 dBV (3.5mm diameter 3-pole locking mini jack, analog output, 0dB audio output level)</p> <p>-20 dBFS (external connection, digital output, 0dB audio output level)</p> <p>-50 dBFS (external connection, analog output, 0dB audio output level)</p>
Analog Audio Output	-12dB - +12dB (3dB step)

Adjustment Range	
Headphone Output Connector	3.5mm diameter mini jack
Headphone Output Level	Max. 10mW (16-ohm)
Tone Signal Frequency	In UWP-D compander mode: 32.382 kHz In UWP compander mode: 32 kHz In WL800 compander mode: 32.768 kHz
Display	OLED
Power Requirements	DC 3.0 V (two LR6/AA size alkaline batteries) DC 5.0 V (supplied from USB Type-C connector)
Battery Life*	Approx. six hours *Battery life has been measured with two Sony LR6/AA size alkaline batteries at 25 °C (77 °F) DISPLAY MODE set to AUTO OFF.
Operating Temperature	0 °C to 50 °C (32 °F to 122 °F)
Storage/Transport Temperature	-20 °C to +55 °C (-4 °F to +131 °F)

Dimensions

63 × 70 × 31 mm (2 1/2 × 2 7/8 × 1 1/4 in.) (W / H / D) (excluding antenna)

---

Mass

Approx. 131 g (4.6 oz) (excluding batteries)

---

## Related products



### **UTX-B40**

UWP-D bodypack transmitter



### **UTX-M40**

UWP-D handheld microphone with unidirectional capsule



### **UTX-P40**

UWP-D XLR plug-on transmitter



### **UWP-D21**

UWP-D bodypack wireless microphone package



### **UWP-D26**

UWP-D bodypack transmitter and XLR plug-on wireless microphone transmitter package



### **UWP-D22**

UWP-D handheld wireless microphone package

## Gallery

