

WD-850

UHF Antenna Divider



Overview

- Provides diversity output for up to four receivers/tuner base units
- Power supplied to the Sony UHF antenna
- Cascade output can be used for an additional antenna-divider or receiver/tuner base unit
- Two pair of antenna input connectors to expand the operating area of a wireless microphone system

Specifications

Group heading

Frequency range	US : 470 to 806 MHz CE : 470 to 862 MHz J : 770 to 810 MHz
-----------------	------------------------------------------------------------------

Channel distribution	Inputs: 2 pairs Outputs: 4 pairs
----------------------	----------------------------------

Antenna Input/Output	BNC-R, 50 ohms
----------------------	----------------

Cascade output	1 pair
----------------	--------

Power supply for antenna booster	
----------------------------------	--

(supplied from antenna input connectors)	DC 9 V/OFF switchable
Power requirements	US: 120 V AC, 60 Hz CE: 230 V, 50 Hz J: AC 100V, 50Hz/60Hz
Power consumption	18 W (when 100mA is being supplied to the antenna booster)
Dimensions (W x H x D)	Approx. 482 × 44 × 285 mm (19 x 1 3/4 x 11 1/4 inches)
Mass	Approx. 4.4 kg (9 lb 11 oz)

Supplied Accessories

Audio output connector	50 ohms terminator (6) AC power cord (1) Operating Instructions (1)
------------------------	---------------------------------------------------------------------------

Related products



DWR-R03D
DWX Series 2-channel digital wireless receiver

Gallery

