

ECM-77BC

Discrete omni-directional lavalier Electret condenser microphone



Overview

The ECM-77 is probably the most often seen lavalier microphone on TV and it is used widely in both studio production and on location. Its popularity is based on a combination of excellent sound quality, robust construction and an attractive cosmetic design. This microphone is the ECM-77BC supplied with a 4-pin locking plug for use with wireless transmitters which have HIROSE SMC9-4S connector.

Hands Free

As a lavalier microphone, the ECM-77 is an alternative to the traditional hand held microphone and being 'hands free' it allows the presenter to concentrate on her/his performance.

Professional Image

The ECM-77 is probably the most seen microphone on TV and its compact design creates a professional image.

Easy and Familiar Operation

The ECM-77 is an essential tool for achieving good quality voice recording. The microphone's capsule is designed for voice pick-up with an extended frequency response and impressive sensitivity. The popularity of the microphone in TV production means that most sound people will be familiar with using the ECM-77.

Features

Designed for high quality voice pick-up

The ECM-77's capsule features a voice emphasis curve, extended frequency response and sensitivity.

Minute size

The capsule has a diameter of only 5.6mm and is 12.5mm long.

Ready for wireless systems

The ECM-77BC is compatible with wireless transmitters which have HIROSE SMC9-4S connector, providing high quality wireless microphone systems for video production.

Specifications

Audio Section

Capsule Type	Electret Condenser
Frequency Response	40 Hz to 20 kHz
Directivity	Omni-directional
Sensitivity *[1]	-39.0 dB (11.2 mV)
Output Impedance *[2]	2.5kΩ±30%, Unbalanced
Dynamic Range	90d B or more
Signal-to-Noise Ratio *[3]	64 dB or more
Inherent Noise *[4]	30 dB SPL or less

Induction Noise From External Magnetic Field *[5]	5 dB SPL or less
---	------------------

Wind Noise *[6]	40 dB SPL or less (with windscreen)
-----------------	-------------------------------------

Maximum Input Sound Pressure Level *[7]	120 dB SPL
---	------------

General Section

Connector	BC type. Supplied with Sony 4-pin (SMC9-4P) connector
-----------	---

Mic Cable	3.9 feet 1.2 m
-----------	-------------------

Power Requirements	DC 1.1 V to 10.0V
--------------------	-------------------

Power Consumption	0.4 mA or less
-------------------	----------------

Dimensions *[8]	φ5.6 X 12.5 mm (Mic head) φ1/4 X 1/2 inches (Mic head)
-----------------	---

Mass	Approx. 25.5 g Approx. 0.9 oz
------	----------------------------------

Supplied Accessories	Single/horizontal type tie clip (1) Metal-mesh type windscreen (1)
----------------------	---

	Wind screen pack Vertical clip pack
--	--

Optional Accessories	Safety pin type clip pack Horizontal double-clip pack Horizontal single-clip pack ECM-77 accessory kit Colored wind screen kit Black windscreen for ECM-77
----------------------	---

Notes

Note	<ul style="list-style-type: none"> *[1] 0 dB = 1 V/Pa, at 1 kHz *[2] Output impedance at 1 kHz *[3] A-weighted, 1 kHz, 1 Pa. *[4] 0 dB SPL = 20 μPa. *[5] dB SPL/1E-7 T, 0 dB SPL = 20 μPa. *[6] Wind noise at 2m/s (0 dB SPL = 20 μPa.) *[8] The values for dimensions are approximate.
------	---

Related products



UTX-B03HR

UWP-D body-pack transmitter



DWT-B01N

DWX series digital wireless body-pack transmitter body-pack

Gallery

