

FW-55BZ40H

55" BRAVIA 4K Ultra HD HDR
Professional Display



Overview

The slim, energy-efficient BRAVIA FW-55BZ40H combines bright 4K HDR image quality with easy operation, flexible networking/control and extensive integration options.

Every BRAVIA 4K Professional Display takes full advantage of latest consumer television technologies to ensure vibrant, high-brightness 4K HDR images that add impact to all your content. Beautiful pictures are balanced by Acoustic Multi-Audio™ for clear, immersive sound.

With portrait mode, advanced control, professional mode, optional interactive compatibility and 24/7 operation, the new BRAVIA FW-55BZ40H is designed to suit a wide range of B2B applications. Side-mounted terminals allow easy access for cable connections. The display's elegantly minimal design is enhanced further for professional use with a four-sided aluminium bezel and full protective rear.

Pro mode allows quick and easy customisation to suit different environments including corporate, education and hospitality, while One Step Setting optimises display settings for signage and conference rooms at the touch of a single button. A powerful SoC platform with improved processing speeds allow apps and animation to run smoothly and efficiently alongside a stress-free user interface for easy operation.

The new BZ Series feature a number of fantastic built-in and optional solutions to customise your BRAVIA exactly the way you want. From meeting room solutions, Manage for TEOS, Connect for TEOS, TDM Digital Signage, Smart Automation System and the Applications Store, without the need for any external devices or players.

For even greater peace of mind there's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

Very high brightness and contrast

The high brightness, high contrast panel with Full Array local dimming is ideal for presenting 4K HDR (High Dynamic Range) content, revealing subtle detail in bright highlights and areas of dark shadow.

See finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

Rich, natural colour with TRILUMINOS Display

TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

Smooth, fluid on-screen action

X-Motion Clarity™ ensures smoother, more natural reproduction of rapidly-moving on-screen images.

Quick set-up with Pro Mode

Customise and store display settings and features, then copy easily to multiple displays via USB flash memory.

One Step Setting

A time-saver in corporate environments, One Step Setting optimises picture and networking settings to suit meeting rooms and signage applications at the touch of a single button.

Easily create digital signage

Integrated support for HTML5 makes it easy to produce compelling digital signage. Combine graphics, text, video and live web content to create attractive signage in minutes with no extra hardware or special training.

Reliable 24/7 operation

BRAVIA is engineered for dependable round-the-clock operation in the most demanding corporate and AV presentation environments.

Cast content with Apple AirPlay2

With Apple AirPlay2 it's easy to stream video and sound to BRAVIA right from an iPhone, iPad or Mac.

Google Chromecast built in

Cast videos and apps from a mobile device directly to BRAVIA with Google Chromecast. Just tap the Cast button on your Android or iOS device screen and instantly enjoy it super-sized on BRAVIA.

Versatile remote control

Control BRAVIA remotely – including on/off, input signal select and adjust volume – over IP via RJ45 by web API or via RS-232C.

Connectivity when you need it most

The FW-55BZ40H supports Wi-Fi 5GHz and 2.4GHz as well as Bluetooth 4.2.

Flexible mounting and installation

The display offers flexible mounting options (vertical, tilt, and table-top), with VESA-standard mounting for easy integration into a wide range of environments.

DICOM

Correctly show X-ray images for non-diagnostic purposes through a dedicated app straight from the home screen. Use DICOM Sim mode to show any HDMI input.

TEOS integration

BRAVIA integrates seamlessly with TEOS, Sony's suite of workspace management applications that orchestrate control of devices and content in boardrooms, meeting areas and public spaces.

Greater Peace of Mind

There's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Specifications

Display Features

| | |
|---------------------------------|---------------------|
| Brightness (cd/m ²) | Typ. 620 / Peak 850 |
|---------------------------------|---------------------|

| | |
|-----------------------|---------|
| Native contrast ratio | 6,000:1 |
|-----------------------|---------|

| | |
|------------------------|----------|
| Dynamic contrast ratio | 550000:1 |
|------------------------|----------|

| | |
|--------------------|---------------|
| Response Time (ms) | 8 |
| Panel type | VA |
| Dimming Type | Local Dimming |
| Display Device | LCD |
| Backlight Type | Direct LED |
| Operation time | 24/7 |
| Portrait mode | Yes |

Display Specifications

| | |
|--|--------------------|
| Wide Screen Size for WEB(diagonal, cm, integer or 1st decimal) | 139.0 cm |
| Display resolution (H x V, pixels) | 3840 x 2160 |
| Screen Size (inch, measured diagonally) | 55" (54.6") |
| Viewing Angle (Right/Left/Up/Down) | 178 (89/89) degree |
| Display Resolution | QFHD |
| Aspect Ratio | 16:9 |

Professional Features

| | |
|--|-------------|
| Professional Hidden Mode | Yes |
| HDMI Auto Wake-up | Yes |
| Multicast/ IPTV | Yes |
| Compatible with TDM Digital Signage/TEOS Solutions | Yes |
| Operating System | Android 9.0 |
| On-board Storage (GB) | 16GB |

Network Features

| | |
|-----------------|--|
| Wi-Fi direct | Yes |
| Wi-Fi Certified | Yes |
| Wi-Fi Standard | a/b/g/n/ac |
| Wi-Fi Frequency | 2.4GHz/5GHz (for Wi-Fi Direct: 2.4GHz Only) |
| Codec for Home | MPEG1:MPEG1/MPEG2PS:MPEG2/MPEG2TS(HDV,AVCHD) |

| | |
|---------|--|
| Network | S):AVC,MPEG4,HEVC/AVI:Xvid,MotinJpeg/ASF(WMV):VC |
|---------|--|

| | |
|--|-----|
| Apple AirPlay (Internet required) | Yes |
|--|-----|

| | |
|------------------------|-----|
| Chromecast built-in | Yes |
|------------------------|-----|

| | |
|-----------------|------------|
| Wireless LAN | Integrated |
|-----------------|------------|

Convenience Features

| | |
|---------------------------|--|
| USB Playback Codecs | MPEG1:MPEG1/MPEG2PS:MPEG2/MPEG2TS(HDV,AVCHD) S):AVC,MPEG4,HEVC/AVI:Xvid,MotinJpeg/ASF(WMV):VC1/ |
|---------------------------|--|

| | |
|--------------|-----|
| HDMI- CEC | Yes |
|--------------|-----|

| | |
|-----------------------|-----|
| On Screen Clock | Yes |
|-----------------------|-----|

| | |
|----------------|-----|
| Sleep Timer | Yes |
|----------------|-----|

| | |
|-----------------|-----|
| On/Off Timer | Yes |
|-----------------|-----|

Display Language AFR,AMH,ARA,ASM,AZE,BEL,BUL,BEN,BOS,CAT,CZE,DAN.

Control Specs

IP Control Yes

RS-232C Control 1 (Side)

Pro mode Yes

Inputs & Outputs

HDMI Signal 4096x2160p(24,50,60Hz),
3840x2160p(24,25,30,50,60Hz),
1080p(30,50,60,100,120Hz),
1080/24p, 1080i(50,60Hz),
720p(30,50,60Hz), 720/24p, 576p,
480p

HDCP HDCP2.3 (for HDMI1/2/3/4)

AC Power Input C8 INLET (REAR)

Composite Video Input(s) 1 (Side)

HDMI Inputs Total 4 (Side)

Digital Audio Output(s) 1 (Side)

Headphone Output(s) 1 (Side)

| | |
|------------------|----------|
| USB Ports | 2 (Side) |
| Ethernet Inputs | 1 (Side) |
| RS-232C Input(s) | 1 (Side) |

Audio Specifications

| | |
|------------------------------------|---|
| Speaker Position | Down Firing |
| Audio Power Output | 10W + 10W |
| Digital Audio Out (Optical) Format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, DTS |
| Dolby Atmos | Yes |
| Speaker Type-2 | X-Balanced Speaker |
| Clear Phase | Yes |
| Dolby Audio Format Support | Dolby Audio, Dolby Atmos |
| HDMI Audio Return Channel(ARC) | Yes (ARC) |
| HDMI Input Audio Format | 5.1 channel linear PCM: 32/44.1/48/88.2/96/176.4/192kHz 16/20/24bits, Dolby Audio, Dolby Atmos, DTS |
| | Two channel linear PCM: 48kHz |

| | |
|-------------------|---------------------------------------|
| ARC Output Format | 16bits, Dolby Audio, Dolby Atmos, DTS |
|-------------------|---------------------------------------|

Video Specifications

| | |
|-----------|--------------------------------------|
| Wide Mode | Auto/Wide zoom/Normal/Full/Zoom/14:9 |
|-----------|--------------------------------------|

| | |
|-------------|-----|
| 4:3 Default | Yes |
|-------------|-----|

| | |
|------------------|------------------|
| Video Processing | 4K X-Reality PRO |
|------------------|------------------|

| | |
|-----------------|-----------------------------|
| Motion Enhancer | X-Motion Clarity, Auto mode |
|-----------------|-----------------------------|

| | |
|--------------|---------------------|
| 4K Processor | X1 4K HDR Processor |
|--------------|---------------------|

| | |
|--|------------------------------|
| HDR (High Dynamic Range) Compatibility | Yes (HDR10,HLG,Dolby Vision) |
|--|------------------------------|

| | |
|-----------------------------------|-------|
| Panel Refresh Rate (Native Hertz) | 100Hz |
|-----------------------------------|-------|

Design Features

| | |
|------------------|-----|
| Cable Management | Yes |
|------------------|-----|

| | |
|-------------|-------|
| Frame color | Black |
|-------------|-------|

| | |
|--------------|-------------------|
| Stand Design | Metal Blade Stand |
|--------------|-------------------|

| | |
|-------------------------------|-----|
| VESA® Hole Spacing Compatible | Yes |
|-------------------------------|-----|

| | |
|-------------------------|----------------|
| VESA® Hole Pitch(W x H) | 30.0 x 30.0 cm |
|-------------------------|----------------|

Eco & Energy Saving

| | |
|---------------------|---|
| Energy Label Rating | G |
|---------------------|---|

| | |
|---------------------------|-------|
| On-mode Power Consumption | 97.0W |
|---------------------------|-------|

| | |
|--------------------------------|-------|
| Power Consumption (in Standby) | 0.50W |
|--------------------------------|-------|

| | |
|-----------------------------|-----|
| Peak Luminance Ratio for EU | 75% |
|-----------------------------|-----|

| | |
|---------------------|-----|
| Mercury Content(mg) | 0.0 |
|---------------------|-----|

| | |
|---|-----|
| Power Saving Mode / Back Light Off Mode | Yes |
|---|-----|

| | |
|------------------------------|-------------|
| Power Requirements (voltage) | AC 220-240V |
|------------------------------|-------------|

Regulatory approvals

| | |
|----------------------|-----|
| Regulatory approvals | CE |
| *1 | CB |
| | EAC |

Dimensions

| | |
|--------------------------|-------------------------------|
| Display only (W x H x D) | Approx. 123.1 × 71.0 × 7.0 cm |
|--------------------------|-------------------------------|

| | |
|--------------------------------|--------------------------------|
| Display with Stand (W x H x D) | Approx. 123.1 × 78.0 × 33.8 cm |
|--------------------------------|--------------------------------|

| | |
|---|--------------------------------|
| Dimension of Package Carton (W x H x D) | Approx. 135.0 × 83.6 × 16.2 cm |
|---|--------------------------------|

Weights (Approx.)

| | |
|--------------|-----------------|
| Display only | Approx. 16.5 kg |
|--------------|-----------------|

| | |
|--------------------|-----------------|
| Display with Stand | Approx. 17.5 kg |
|--------------------|-----------------|

| | |
|-----------------------|-------|
| Package Carton(Gross) | 24 kg |
|-----------------------|-------|

Optional Accessories

| | |
|-------------------|---|
| Wallmount Bracket | SU-WL450 (Terminal access limitation, refer to SU-WL450 product page), SU-WL850, SU-WL500 |
|-------------------|---|

PrimeSupport

3 years warranty with Repair or if

Included
PrimeSupport

necessary advanced exchange
handled by local partner, on
premise where possible.

Optional
PrimeSupport
Extensions

Optional 2-year support extension
available: PSP.FDWBZH55.2X

Notes

*1

The information on this page is
current as of the date of
publication. Please contact your
local office for the latest
information.

Further Information

Product

Information Sheet <https://eprel.ec.europa.eu/screen/product/electronic>

Gallery



