

## HDC-5500V

2/3-inch 4K 3-CMOS sensor  
portable system camera



NETWORKED **LIVE**

### Specifications

#### General

Power requirements AC 240 V, 1.4 A (max.), DC 12 V, 9.5 A (max.), DC 240 V, 1.05 A (max.)

Operating temperature -20°C to +45°C (-4°F to 113°F)

Storage temperature -20°C to +60°C (-4°F to +140°F)

Mass Approx. 5.1 kg (11 lb 3.9oz)  
(unit only)

Dimensions (W x H x D)  
[Hood is not included.] 138 x 268 x 363

#### Imager

Imager 2/3 inch type 4K CMOS sensor with global shutter

Method 3-CMOS, RGB

---

Effective resolution (H x V)	QFHD: 3840 × 2160 HD: 1920 × 1080
------------------------------	--------------------------------------

---

## Electrical characteristics

Sensitivity	F10 with 1080/59.94p F11 with 1080/50p (at 2,000 lx with 89.9% reflectance)
Signal-to-noise ratio	-62 dB
Geometric distortion	Negligible (not including lens distortion)

---

## Optical system specifications

Spectrum system	F1.4 prism
Built-in filters	ND filters 1: CLEAR, 2-5: Variable ND (1/3-1/256)

---

## Input/output connectors

CCU	Optical/electrical multi connector (LEMO 3K.93C connector) (x1)
LENS	12-pin (x1)
VF	20-pin (x1)

---

MIC 1 IN	XLR 3-pin, female (x1)
AUDIO IN CH1, CH2	XLR 3-pin, female (x1 each) When AUDIO switch is set to MIC: –60 dBu (can be selected up to –20 dBu by menu operation), balanced When AUDIO switch is set to LINE: 0 dBu, balanced
INTERCOM 1, INTERCOM 2	XLR 5-pin, female (x1 each)
EARPHONE	4-pole mini jack (x1), (3-pole stereo, 4-pole CTIA standard, 4-pole OMTP standard)
DC IN	XLR 4-pin (x1), DC 10.5 to 17 V
DC OUT	4-pin (x1), DC 10.5 to 17 V, max. 0.5 A <sup>*1</sup> 2-pin (x1), DC 10.5 to 17 V, Max. 2.5 A <sup>*1</sup>
SDI 1	BNC (x1)
SDI 2	BNC (x1)
SDI MONI	BNC (x1)
TEST OUT	BNC (x1) BNC (x1) PROMPTER 1 Vp-p, 75 Ω

PROMPTER/GENLOCK	GENLOCK HD: SMPTE ST274, tri-level sync, 0.6 Vp-p, 75 Ω, SD: Black burst (NTSC: 0.286 Vp-p, 75 Ω/PAL: 0.3 Vp-p, 75 Ω)
PROMPTER2	No
RET CTRL	6-pin (x1)
REMOTE	8-pin (x1)
TRACKER	12-pin (x1)
CRANE	12-pin (x1)
USB	USB 2.0 Type A 4-pin (x1) (for connecting USB drive)
NETWORK TRUNK	RJ-45 type 8-pin (x1)

## Supplied accessories

Before Using This Unit (1),  
Operating Instructions (CD-ROM)  
(1),  
Cable clamp belt (1 set),  
Screws (+B3×8) (2),  
Attached label (1)

## Notes

\*1

This may be limited by the imposed load or inputs.

## Related products



### RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



### RCP-3100

Joystick type of remote control panel for HDC/HSC/HXC series cameras. 5 units in 19-inch EIA rack.



### RCP-1000

Joystick type of simple Remote Control Panel for HDC/HSC/HXC series cameras. 6 units in 19-inch EIA rack.



### MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



### MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



### HKC-TR37

Digital Triax Transmission Adaptor for HDC camera series



### HKC-WL50

Wireless transmission adaptor for HDC-5500 and HDC-3500



### HKCU-REC55

Recording option for HKCU-5500 and HKCU-3500 CCU



### HKCU-REC50

Recording option for HKCU-5000



### HKCU-UHF50

4K 4x processor board for HKCU-5000

## Gallery

