

## HDLA-1500

### HD Large Lens Adaptor



### Overview

The HDLA-1500 allows operation of the HDC-1500 HD portable camera or HDC-3300 SuperMotion camera together with large studio/OB lenses and 7" viewfinders. Unlike traditional lens "build-up kits", the HDLA-1500 provides a very simple one-touch cable-free mounting of the camera so that it can be quickly and easily converted from hand-held to tripod configuration.

#### Note

The HDLA-1500 is finished in a pale grey body colour, the same as the HDC-1000 studio camera. If required, a dark coloured version, HDLA-1500/B is also available.

#### **One-touch instant docking mechanism**

The camera can be fitted quickly and easily into the adaptor. This unique mechanism allows the HDC-1500 to be attached and detached without removing the large lens.

#### **Quick mounting for portable camera head**

To provide efficient operation in studio or OB environments, the large lens adaptor has a unique design which allows the camera to be converted from hand-held to large lens configuration in just a few seconds.

#### **Cable-free operation with all connections contained in "hot shoe" mounting**

Utilizing a newly developed interlocking mechanism, power,

video, and control signals are passed on directly from the HDC-1500 to the HDLA-1500, without requiring additional cable connections

### **Built-in teleprompter power supply**

Utility power (200-240V AC) is available from the large lens adaptor, when used in conjunction with the HDCU-1000 camera control unit

### **Same handling characteristic as full size camera**

All the control features and functionality traditionally associated with full size cameras are provided in this efficient operational package. The HDLA-1500 also has a viewfinder position which is notably lower than the comparable models. This low-profile design significantly improves the operator's view, as well as minimizes the parallax between the optical axis of the camera head and viewfinder.

## Features

### **New low profile design with lower viewfinder height**

### **Adjustable viewfinder position**

### **Direct docking mechanism**

## Related products



### **HDCU-5000**

Camera Control Unit (CCU) for HDC-5500 and HDC-3500/3100 series system cameras



### **HDVF-EL780**

Full HD 7.4-inch OLED viewfinder

## Gallery

