

# Interactive Overlays

Interactive Overlays for 43", 49", 55", 65", 75", 85" and 100" Professional Displays



## Overview

### **Add the power of touch**

Available to suit screen sizes from 43" up to 100", these slim, easy-fit touchscreen overlays transform Professional Displays\* into a large touch-enabled interactive screen that's ideal for a wide range of corporate and educational applications.

Reliable, accurate IR or capacitive (PCAP) touch technology ensures smooth, responsive operation with ten touch points. The overlay's tough anti-glare surface ensures optimum visibility, even in sunny environments.

Our touch-enabled Professional Displays\* are ideal for a wide range of interactive signage and information kiosk applications – from schools, universities, museums, libraries, boardrooms and offices to hotel lobbies, hospitality zones, retail stores and visitor attractions.

\*Professional Displays available separately

## Features

### **Engage audiences with a touch**

Responsive, high quality touchscreen overlay transforms your Professional Display (available separately) into a super-size touch enabled interactive terminal.

### **Responsive, accurate multi-touch performance**

Audience engagement is right at your fingertips. Customers can't keep their hands off these big, beautiful screens: 10 multi-touch points ensure accurate, responsive performance across the entire display area.

### **Wide range of screen size options**

There's a full range of touch overlays, offering guaranteed compatibility with current Professional Display models in screen sizes from 43" right up to 100" (PCAP models up to 75").

### **Big audience appeal, low running costs**

Powered by direct USB connection, the energy-efficient touch overlay keeps running costs down (display is powered separately).

### **Looks great in every light**

The touch overlay's tough anti-glare surface ensures optimum visibility, even in the sunniest environments.

### **Quick and easy to install and set up**

Fuss-free installation and set up allows deployment of your interactive touchscreen solution in minutes.

### **Add that finishing touch**

Tailor your touchscreen with an optional overlay cover. There's a choice of attractive cover designs and colours that blend beautifully into any environment.

## Specifications

IR	
Overlay - Size (diagonal)	43", 49", 55", 65", 75", 85", 100"
Design - Color	Black
Design - Bezel size (mm)	43-55": 25mm 65-75": 28mm 85-100": 30mm
Glass - Anti-glare	Yes
Glass - Thickness	43-55": 3mm 65-75": 4mm 85-100": 5mm
Technology	IR
Technology - Number of touch points	10 points
Technology - Response time	<8ms
Technology - Max touch point accuracy	1mm
Technology - Touch durability	Unlimited
Power - Power input	USB HID. No driver required
Power - Power consumption (W)	<2.5W
Environment - Operating Temperature	-20°C - 70°C
Environment - Storage Temperature	-40°C-85°C
Environment - Operating Humidity	10%-90% RH (non-condensing)
Environment - Storage Humidity	10%-90% RH
Dimensions - Overlay Only (WxHxDmm) (Approx.)	43": 997 x 584 x 30 mm 49": 1126 x 660 x 31 mm 55": 1262 x 737 x 32 mm 65": 1489 x 864 x 36 mm 75": 1708 x 988 x 30 mm 85": 1968 x 1160 x 30 mm 100": 2360 x 1400 x 40 mm
Dimensions - Package Carton (WxHxDmm) (Approx.)	43": 1080 x 600 x 150 mm 49": 1260 x 760 x 150 mm 55": 1380 x 860 x 150 mm 65": 1615 x 990 x 150 mm 75": 1870 x 1150 x 150 mm 85": 2090 x 1280 x 150 mm 100": 2480 x 1500 x 600 mm

## IR

Weight - Overlay Only (Kg) (Approx.)	43": 7
	49": 9
	55": 12
	65": 18
	75": 30
	85": 50
100": 75	

Weight - Package Carton (Kg) (Approx.)	43": 11
	49":13
	55": 15
	65": 21
	75":35
	85":58
100":80	

## Capacitive

Overlay - Size (diagonal)	43", 49", 55", 65", 75"
---------------------------	-------------------------

Design - Color	Black
----------------	-------

Design - Bezel size (mm)	43": 33mm
	49-55": 30mm
	65": 36mm
	75": 51mm

Glass - Anti-glare	Yes
--------------------	-----

Glass - Thickness (mm)	43-65": 4mm
	75": 5mm

Technology	Capacitive
------------	------------

Technology - Number of touch points	43-75": 10 points
-------------------------------------	-------------------

Technology - Response time	<16ms
----------------------------	-------

Technology - Max touch point accuracy	3mm
---------------------------------------	-----

Technology - Touch durability	Unlimited
-------------------------------	-----------

Power - Power input	USB HID. No driver required
---------------------	-----------------------------

Power - Power consumption (W)	<2W
-------------------------------	-----

Environment - Operating Temperature	-20°C - 60°C
-------------------------------------	--------------

Environment - Storage Temperature	-20°C - 60°C
-----------------------------------	--------------

Environment - Operating Humidity	10%-90% RH (non-condensing)
----------------------------------	-----------------------------

## Capacitive

Environment - Storage  
Humidity

10%-90% RH

Dimensions - Overlay Only  
(WxHxDmm) (Approx.)

43": 1009 x 597 x 60 mm  
49": 1139 x 669 x 60 mm  
55": 1272 x 747 x 60 mm  
65": 1502 x 877 x 60 mm  
75": 1757 x 1035 x 65 mm

Dimensions - Package Carton  
(WxHxDmm) (Approx.)

43": 1080 x 600 x 150 mm  
49": 1260 x 760 x 150 mm  
55": 1380 x 860 x 150 mm  
65": 1615 x 990 x 150 mm  
75": 1870 x 1150 x 150 mm

Weight - Overlay Only (Kg)  
(Approx.)

43": 7.5 kg  
49": 9.5 kg  
55": 12.5 kg  
65": 18.5 kg  
75": 30.5 kg

Weight - Package Carton (Kg)  
(Approx.)


43": 11.5 kg  
49": 13.5 kg  
55": 15.5 kg  
65": 21 kg  
75": 35 kg

## Service and warranty

Warranty

3 years with advanced exchange

# Gallery





---

© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.