

5,000 lumens WUXGA 3LCD installation projector (colour availability may vary by country)



Overview

Black and lensless models available in Europe; please check for local availability.

Features

Very high image quality with BrightEra 3LCD projection engine

Advanced picture refinement technologies

Crisp, detail-packed WUXGA resolution images

Hassle-free automatic filter cleaning

Powered Wide Lens Shift

Included powered standard zoom lens plus wide choice of lens options

Supports HDBaseT

Create super-size displays with Edge Blending

Project onto non-flat surfaces with Image Warping

Quiet operation



Slim, attractive new blend-in design


Choice of Picture Modes


Simple set-up with friendly new Installation menu


Project Side by Side


Specifications






















Gallery

