

AN-820A

The AN-820A is an active antenna Sony wireless microphone rack receivers



Overview

The AN-820A is an active antenna compatible for the Sony DWR-R02DN and MB-X6 rack receiver systems. The antenna enhances the performance of the wireless microphone, extending the operating range and immunity to 'drop outs'. It is a compact unit that can be mounted on a wall bracket or a microphone stand. Normally a pair of AN-820A will be configured in the system, for diversity reception.

The AN-820A is available in four versions, covering different frequency ranges

LL: 470 MHz to 542 MHz

L: 556 MHz to 662 MHz

M: 638 MHz to 758 MHz

H: 758 MHz to 862 MHz

Enhanced performance

The AN-820A allows the performance of the wireless microphone system to be enhanced, extending operating ranges and immunity to 'RF drop outs'.

The AN-820A is particularly useful in enhancing performance in larger multi-channel systems (more than 4 wireless microphone systems).

Simple to use

Whether the wireless microphone system is a fixed installation or mobile, the AN-820A is simple to use. The antenna weighs only 250g and can be mounted on a wall or a microphone stand, both mounting brackets are supplied. In addition, the antenna powering status is displayed by an LED.

Features

Built power amplifier

The AN-820A has a built in 10dB power amplifier to boost the strength of the received signal

Compatible with Sony wireless rack receivers

The AN-820 is compatible with the DWR-R02DN or MB-X6 and URX-M2 modular rack receivers. Typically a pair of rack receivers are configured by diversity reception.

Compact and discrete cosmetic design

AN-820 is only 177 mm tall and it has an discrete cosmetic design. It is therefore easy to mount the unit in virtually any venue (ie theatre or corporate meeting room), without it being easily seen.

Specifications

Type

Frequency Code	LL, L, M, H
----------------	-------------

Antenna Section

Antenna Type	Dipole
--------------	--------

Directivity	Horizontal omnidirectional
-------------	----------------------------

	M: 638 MHz to 758 MHz
--	-----------------------

Frequency Range	LL: 470 MHz to 542 MHz L: 556 MHz to 662 MHz H: 758 MHz to 862 MHz
-----------------	--

Booster Section

Frequency Range	M: 638 MHz to 758 MHz LL: 470 MHz to 542 MHz L: 556 MHz to 662 MHz H: 758 MHz to 862 MHz
-----------------	---

Booster Gain	18 +12 dB (with 12 V DC) 10 ± 12 dB (with 9 V DC)
--------------	--

Voltage Standing Wave Ratio	3.0 or less
-----------------------------	-------------

Noise Figure	4 dB or less
--------------	--------------

Third Order Intermodulation	60 dB or more (85 dB μ VEMF input)
-----------------------------	--

Input/Output

Output Connector	BNC-R, 50 Ω
------------------	--------------------

General

Power Requirements	9 V/12 V DC
--------------------	-------------

Power Consumption	50 mA or less
Operating Temperature	32°F to 122°F 0°C to 50°C
Storage/Transport Temperature	-4°F to +140°F -20°C to +60°C
Dimensions *[1]	Approx. 70 × 117 × 132 mm (W x H x D) Approx. 2 7/8 x 4 5/8 x 5 1/4 inches (W x H x D)
Mass	Approx. 9 oz Approx. 270 g
Supplied Accessories	Warranty Card (1) Wall mounting attachment(1) Power utility box mounting attachment (1) Operating Instructions (1) Mounting screws (1 set) Microphone stand mounting adapter (PF 1/2 screw) (1)

Notes

Note

*[1] The values for dimensions are approximate.

Gallery

