

HZC-QFR50 / HZC-QFR50M / HZC-QFR50W

Max. HD 4x Slow motion with HDC-3500 system camera and others



Overview

Software licenses for shooting Max. HD 4x slow motion with HDC-3500 system camera and others

HZC-QFR50, HZC-QFR50M and HZC-QFR50W are the software licenses on the HDC-3500 for shooting Max. HD 4x slow motion.

The HZC-QFR50 can be permanently used.

The HZC-QFR50M can be used for 30 days.

The HZC-QFR50W can be used for 7 days.

Activation key for pre-installed software.

Related products



HKC-WL50

Wireless transmission adaptor for HDC-5500 and HDC-3500



HDC-3500

Three 2/3-inch 4K CMOS sensors portable system camera for fibre operation



HDC-5500

High performance three 2/3-inch 4K CMOS sensor portable system camera with direct 4K output



HDC-P50

4K/HD compact POV system camera

Gallery

