

UNI-OPL7C3

Outdoor Pressurized dome camera housing



Overview

Applicable Camera Models;
- SNC-RX550P - SNC-RX530P - SNC-RX570P Fixing Method;
- SNCA-WM20G (wall) - SNCA-CEILING (ceiling) - SNCA-WM20FC (see note) Rating;
- IP67 Operating Temperature;
- -29°C to +50°C (SNCA-HEATER) Voltage;
- 24 volts AC Optional accessories;
- SNCA-CLEAR/2 (included)
- SNCA-TINTED/2

Related products



SNC- EB600

Box-type 720p/30 fps
Camera Powered by
IPELA ENGINE EX™ - E
Series



SNC- EB600B

Basic Box-type
720p/30 fps Camera
Powered by IPELA
ENGINE EX™ - E Series



SNC- EB630

Box-type 1080p/30 fps
Camera Powered by
IPELA ENGINE EX™ - E
Series



SNC- EB630B

Basic Box-type
1080p/30 fps Camera
Powered by IPELA
ENGINE EX™ - E Series



SNC-



SNC-



SNC-



SNC-

VB600

Box-type 720p/60 fps
Camera Powered by
IPELA ENGINE EX™ - V
Series



EP521

Standard Definition
(PAL) PTZ Network
Camera



EP580

1080p/30 fps PTZ
Camera - E Series

ER521

Standard Definition
(PAL) Rapid Dome
Network Camera

SNC- ER550

720p/30 fps Rapid
Dome Camera - E
Series

SNC- ER580

1080p/30 fps Rapid
Dome Camera - E
Series

Gallery

