

BC-U2A

Two-channel simultaneous battery charger/AC adaptor for BP-U90/U60/U60T/U30 Lithium-ion battery



Overview

Charges two BP-U90/U60/U60T/U30 batteries

The BC-U2A battery charger can simultaneously charge two compact BP-U90, BP-U60 / 60T or BP-U30 Lithium-ion batteries at high speed

Built-in AC adaptor provides 12 V DC power output while charging one battery

The BC-U2A also has 12 V DC power output cable to power a camcorder directly, while charging one battery simultaneously.

Portable design for ease of use

The BC-U2A has a mass of 620 g (1 lb 6 oz) and dimensions (W x H x D) of 177 x 53.2 x 137 mm (7 x 8 1/8 x 5 1/2 inches).

NOTE: BC-U2A is compliant with safety standard IEC62368-1.

Specifications

General

Power Requirements	AC100V ~ 240V 50/60Hz
--------------------	-----------------------

Power consumption	89W
-------------------	-----

DC supply	[36W] 12V / 3.0A
Charging Voltage	16.4V
Dimensions (W x H x D)	177x53.2x137 (mm)
Mass	620 (g) +DC out cable
Operating Temperature	[DC supply]-5 °C ~ +45°C [Charge] 0°C ~ +45°C

Approximate charge times

BP-U90	190 minutes
BP-U60 / 60T	150 minutes
BP-U30	130 minutes

Supplied Accessories

Supplied Accessories	Instruction manual Warranty Paper DC out cable
----------------------	--

Related products



PXW-X200

Three 1/2-type Exmor™ CMOS Full HD sensor XDCAM camcorder with 17x zoom lens and XAVC recordings



PXW-FS7M2

4K Super 35mm Exmor CMOS sensor XDCAM camera with Variable ND Filter, E-Mount



PXW-X180

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and wireless operations,



PXW-Z280

World's first 4K Handheld Camcorder with 1/2-type 3CMOS with 4K 50p/60p recording capability,

(Lever Lock), 4K/2K RAW and XAVC recording

including XAVC recordings

12G-SDI, Dual Link Cellular capability, 17x zoom lens, advanced Face Detection AF



PXW-FS5

Grab and Shoot with handheld Super 35



PXW-Z190

4K Handheld Camcorder with all-new 1/3-type 3CMOS with 4K 50p/60p* recording capability, 25x zoom lens and advanced Face Detection AF



PXW-X160

Three 1/3-inch type Exmor™ CMOS Full HD sensor XDCAM camcorder with 25x zoom lens and XAVC recordings



PMW-300K1

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 14x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps



PXW-FS5M2

'Grab and shoot' Super35 handheld camcorder with stunning new creative look, 4K 120fps HFR and HDR, α Mount lens system, Variable ND Filter, 4K/2K RAW and XAVC recording



PMW-300K2

Three 1/2-inch Exmor™ CMOS sensors semi-shoulder XDCAM camcorder with interchangeable 16x zoom HD lens system recording XAVC HD 100 Mbps and MPEG HD422 at 50 Mbps

Gallery

