

## BVM-HX1710

16.5-inch 4K TRIMASTER HX™  
Professional Master Monitor



4K

SR Live  
for HDR

HDR

### Specifications

#### Picture Performance

Panel ·  $\alpha$ -Si TFT Active Matrix LCD

Picture Size (diagonal) 16.5 inches (420.3 mm)

Effective Picture Size (H x V) 366.3 x 206.1 mm (14 1/2 x 8 1/8 inches)

Resolution (H x V) 3840 x 2160 pixels

Aspect 16:9

Pixel Efficiency 99,99%

Display Colours 1.07 billion

Panel Frame Rate 96 Hz / 100 Hz / 120 Hz (96 Hz and 120 Hz are also compatible with 1/1.001 frame rates)

Viewing Angle (Panel) 89°/89°/89°/89°  
(up/down/left/right contrast >

Specification)	10:1)
Normal Scan	0% scan
Underscan	3% underscan
Colour Temperature	D50, D60, D65, D93, DCI*1, and user 1–10 (5,000 K to 10,000 K adjustable), DCI XYZ
Luminance	3000 cd/m <sup>2</sup> (typical)*2 700 cd/m <sup>2</sup> (typical)*3
Colour Space (Colour Gamut)	ITU-R BT.2020*4, ITU-R BT.709, EBU, SMPTE-C, DCI-P3*4, S-Gamut3*4, S-Gamut3.Cine*4
Transmission Matrix	ITU-R BT.2020 (Non-constant luminance is supported), ITU-R BT.709
EOTF	2.2, 2.4, 2.6, CRT, 2.4 (HDR), S-Log3, S-Log3 (Live HDR), SMPTE ST 2084, ITU-BT.2100 (HLG)
Warm-up Time	Approx. 30 minutes To provide stable picture quality, turn on the power of the monitor and leave it in this state for more than 30 minutes.

## Input

SDI	(12G/6G/3G/HD-SDI) BNC (x2), (3G/HD-SDI) BNC (x2), Input impedance: 75 $\Omega$ unbalanced
HDMI Input	HDMI (HDCP2.3/1.4) (x1)
Parallel Remote	RJ-45 8-pin (x1) (Fixed pin assignment)
Serial Remote (LAN)	Ethernet, 10BASE-T/100BASE-TX RJ-45 (x1)
USB Input	USB (USB2.0) connector (x1)

## Output

Enhanced Monitor Output	(12G/6G/3G/HD-SDI) BNC (x1), Output impedance: 75 $\Omega$ unbalanced *5
SDI Output	(12G/6G/3G/HD-SDI) BNC (x2), (3G/HD-SDI) BNC (x2), Output impedance: 75 $\Omega$ unbalanced

## General

Power Requirement	AC 100 V to 240 V, TBA A to TBA A, 50/60 Hz
-------------------	--

Power Consumption	Approx. TBA W (max.) 0.3 W In off-mode (When the Power switch is off)
Off Mode Activated	After About 60 Minutes
Operating Temperature	0°C to 35°C (32°F to 95°F) Recommended: 20°C to 30°C (68°F to 86°F)
Operating Humidity	30% to 85% (no condensation)
Operating Pressure	700 hPa to 1060 hPa
Dimensions (W x H x D)	TBA x TBA x TBA mm (TBA x TBA x TBA inches)
Mass Approx.	TBA Kg (TBA lb TBA oz)
Supplied Accessories	AC power cord (1)AC plug holder (1)Before Using This Unit (1)

## Notes

\*1 DCI: x=0.314, y=0.351

\*2 This luminance value is a typical value at D65 (x, y = 0.3127, 0.329) with a 10% white window. This value is not guaranteed. To avoid irreversible panel damage, an auto brightness limiter is enabled if the

total amount of current or screen temperature exceeds the maximum capacity of the BVM-HX1710.

\*3

Panel specification (all white signal). This luminance value is typical at D65 (x, y = 0.3127, 0.329) and is not guaranteed.

\*4

The BVM-HX1710 does not cover selected colour space in full.

\*5

Either BVML-H10, BVML-S10 or BVML-T10 optional license is required.

## Related products



### **BVMK-R10**

Monitor Control Unit



### **FWD-55A95L**

55" Sony BRAVIA OLED 4K HDR Display with Google TV, including 3 years PrimeSupport



### **BVML-F10**

Fast response license for for BVM-HX3110/ HX1710/ HX1710N



### **BVML-H10**

HDR-SDR conversion license for BVM-HX3110/ HX1710/ HX1710N



### **BVML-T10**



### **BVML-S10**

3D LUT output license for BVM-HX3110/HX1710/HX1710N    Signal conversion output license with a 3D LUT feature for BVM-HX3110/ HX1710/ HX1710N

## Gallery

