


## File Server mode License for FM2

File Server mode License of FM2(FSL) is an option license for File Manager2. The license enables standard file IO interface of File Manager2, and it can be usable by local or network applications (SMB).



### Overview

File Server mode License of FM2(FSL) is an option license of File Manager2.

The license enables standard file IO interface of File Manager2 and it can be usable by local or network applications (SMB).

Note: if you would like to use FSL, you must first install File Manager2 software and activate the File Manager2 license.

**This product is an activation key for pre-installed software.**

### Features

Enables File Server mode of File Manager2

### Specifications

Please review File Manager2 manual

## Related products



### ODS-D55U

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)



### ODS-D77F

Optical Disc Archive fibre channel drive unit for ODS-L30M PetaSite scalable library with transfer speeds up to 1,150 Mbps (read) and 780 Mbps (write-once disc) or 310 Mbps (rewritable disc)



### ODS-L100E

PetaSite Optical Disc Archive library expansion unit (cartridge only)



### ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



### ODS-D280U

Optical Disc Archive stand-alone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



### ODS-D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.



### Optical Disc Archive Cartridge Generation 1

300GB\*, 600GB, 1.2TB and 1.5TB disc (Rewritable or Write once)  
 ODC300R, ODC300RE, ODC600R, ODC600RE, ODC1200RE, ODC1500R



### ODS-L30M

PetaSite Optical Disc Archive 30-slot master library unit



## **ODS-L60E**

PetaSite Optical Disc Archive library expansion unit (drive and cartridge)

## **ODS-D380U**

The latest Optical Disc Archive stand-alone drive with very high transfer speeds of 1.5 Gbps write (verify on) and 3 Gbps read using ODC-5500R Generation3 cartridge.

## **File Manager2**

File Manager2 (FM2) is a successor software to the existing File Manager software. FM2 allows the ability to archive / retrieve your contents to / from Optical Disc Archive Drive and PetaSite Library from a PC.

## **ODS-L10**

Optical Disc Archive 10-Slot library

## Gallery

