

## HSCU-300RF

Compact Camera Control Unit  
for HSC-300RF and HSC-100RF  
cameras



### Overview

#### **Simple and yet versatile system configuration over 1.5 Gbps optical fibre**

The highly compact 1.5 RU-size HSCU-300RF Camera Control Unit creates a standardised 19-inch rack system that is ideal for space-limited production areas. When the front panel of the HSCU-300RF is replaced with the optional CCU Front Control Panel HKCU-FP2, a simple remote control system can be configured. Many functions of the camera can be controlled by the control knobs and switches on the HKCU-FP2.

#### **Multiple camera control**

Furthermore, when the optional HZCU-MC3 camera operating software is installed, the HSCU-300RF allows the HSC-300RF or the HSC-100RF to be controlled by an MSU-1000/1500 Master Setup Unit or RCP-1000 series Remote Control Unit, enabling the HSC-300RF to be used as a simple studio system or as part of a large-scale broadcasting system consisting of multiple cameras.

## Gallery

