

## SNC-EB630

Box-type 1080p/30 fps Camera  
Powered by IPELA ENGINE EX™ -  
E Series



### Overview

**Excellent image quality is even more affordable with this versatile Full HD network camera that's ideal for everyday security applications.**

This easy to install fixed network camera brings crisp Full HD imaging quality to a wide range of indoor security and surveillance applications, from offices, banks and retail spaces to education.

Sony's Exmor CMOS sensor captures crisp, clear, low-noise Full HD images for dependable monitoring – even in tricky low-light situations.

As a part of Sony's latest generation of video security cameras, the SNC-EB630 features Sony's award winning IPELA ENGINE EX processing platform. This boosts image quality in a wide range of environments, including challenging low-light scenes.

View-DR expands dynamic range for significantly improved imaging in high-contrast and strongly backlit scenes, like sun-drenched offices or car park entrances. Image stabilisation keeps video images crisp and clear, even when the camera is subject to vibration on a mounting pole or bracket.

## Features

### **See every scene clearly with Full HD image quality**

View fine detail in a wide range of everyday video security and surveillance environments, from retail spaces to banks and schools. The high resolution Exmor CMOS sensor assures crisp, clear Full HD 1080p images – even in low light conditions like dimly-lit car parks.

### **Best-ever imaging performance with IPELA ENGINE EX**

At the heart of Sony's latest generation of cameras, the powerful IPELA ENGINE EX processing platform combines several technologies for optimises Full HD picture quality. View-DR combines images taken at different shutter speeds, delivering a wide dynamic range up to 90 dB for excellent performance in high contrast, strongly backlit environments.

### **Steadier, more stable video footage**

The in-built image stabiliser minimises the effects of camera shake – for example when the camera's pole mounted or subject to mechanical vibration. With clearer, more stable video images it's easier to see what's happening in any scene.

### **Don't miss that crucial moment with Intelligent Motion Detection and Face Detection**

In-built motion detection can trigger a range of actions, from storage and transfer of images to sounding of external alarms. False alarms caused by noise, weather and environment noise are minimised by a smart processing algorithm. Human face detection is also supported, allowing rapid indexing of recordings to find events where a face is visible in the scene.

### **Detect in confidence with Edge-based Analytics**

Powerful DEPA Advanced video analytics enhances Intelligent Motion Detection with rule-based alarm triggers, providing alerts with object filters like 'passing' and 'intrusion' to further reduce false alarms.

## **Reduce cabling costs with Power Over Ethernet (PoE)**

Power over Ethernet (PoE) allows the camera be powered using the same Ethernet cable that's for data transfer, reducing installation complexity and costs.

## **View and control with your smartphone**

Remotely view live camera images with your Android or iOS smartphone or tablet. You don't even need to download a special app.

## **ONVIF (Open Network Video Interface Forum) compliance**

Support for ONVIF simplifies interoperability with other network video devices. The ONVIF (Open Network Video Interface Forum) defines a common protocol for the exchange of information between network video devices, including automatic device discovery and video streaming.

## **Triple streaming for extra operational versatility**

Configure up to three simultaneous IP video streams to suit your operating needs. For example, one stream for high quality live viewing; another for storage-efficient recording; and a third for viewing over a low bandwidth connection or on mobile devices.

## **Day/Night operation for clearer images around the clock**

In extreme low light conditions the camera switches automatically to a special night-time monitoring mode, removing the IR-cut filter and extending sensitivity to infra-red wavelengths. Sophisticated video processing ensures crisp, clearly-visible colour images in light levels as low as 0.1 lx. During the day, the IR-cut filter assures excellent image clarity and colour accuracy, even in bright sunlight.

## Specifications

### Camera

Image Sensor	1/2.9-type progressive scan Exmor CMOS sensor
Number of Effective Pixels	Approx. 2.14 Megapixels
Signal System	NTSC/PAL (switchable)
Sync System	Internal synchronization
Minimum Illumination (50 IRE)	Color: 0.1 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0.07 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps)
Minimum Illumination (30 IRE)	Color: 0.06 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0.05 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps)
Dynamic Range	Equivalent to 90 dB with View-DR technology
S/N Ratio (Gain 0 dB)	More than 50 dB
Gain	Auto
Shutter Speed	1/1 s to 1/10,000 s
Exposure Control	Exposure compensation, Shutter speed, Iris

White Balance	ATW, ATW-PRO, Fluorescent lamp, Mercury lamp, Sodium vapour lamp, Metal halide lamp, White LED, One push WB, Manual
Lens	CS-mount varifocal lens
Zoom Ratio	Optical zoom 2.9x Digital zoom 4x Total zoom 11.6x
Easy Focus for Setup	Yes
Horizontal Viewing Angle	114.2° to 40.0°
Vertical Viewing Angle	60.6° to 22.5°
Focal Length	f = 2.8 mm to 8.0 mm
F-Number	F1.2 (Wide) to F1.95 (Tele)
Minimum Object Distance	300 mm

## Camera Features

Day/Night	True D/N
Day/Night linked with Easy Focus	Yes

Image rotate	90°, 270°
Mirroring	Yes
Wide-D	View-DR
Tone Correction	Visibility Enhancer
Noise Reduction	XDNR
Image Stabilizer	Electronic
Picture Mode	Yes
Privacy Masking (number)	20
Privacy Masking (shape)	Quadrangle formed by any four corner points
Privacy Masking (color/effect)	Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic
Superimpose Number	3 independent positions for characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for logo marks
Superimpose Language	English

Menu Language	English, Japanese, Chinese (simplified), Chinese (traditional), French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai
---------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------

Smartphone viewer	Yes
-------------------	-----

## Video

Resolution	1920 x 1080, 1280 x 720, 1024 x 576, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 640 x 360, 352 x 288, 320 x 184 (H.264, JPEG)
------------	--------------------------------------------------------------------------------------------------------------------------------

Compression Format	H.264 (High/Main/Baseline Profile), JPEG
--------------------	------------------------------------------

Maximum Frame Rate	H.264: 60 fps (1920 x 1080) JPEG: 30 fps (1920 x 1080)
--------------------	-----------------------------------------------------------

Bitrate Control Mode	CBR/VBR (selectable)
----------------------	----------------------

Range of Bit Rate Setting	64 Kbps to 32 Mbps
---------------------------	--------------------

Solid PTZ	Yes
-----------	-----

Adaptive Rate Control	H.264
-----------------------	-------

Bandwidth Control	JPEG
-------------------	------

Multi streaming Capability	Yes (3)
----------------------------	---------

Number of Clients	20
-------------------	----

## Intelligent Video/Audio Analytics

Analytics Architecture	DEPA Advanced
------------------------	---------------

Intelligent Motion Detection	Yes
------------------------------	-----

Face Detection	Yes
----------------	-----

Tamper Alarm	Yes
--------------	-----

Scene Analytics	Passing, Intrusion, Left Object Detection, Removed Object Detection
-----------------	---------------------------------------------------------------------

## System Requirements

Operating System	Windows XP (32 bit) Professional Edition Windows Vista (32 bit) Ultimate, Business Edition Windows 7 (32/64 bit) Ultimate, Professional Edition Windows 8 Pro (32/64 bit) Windows 8.1 Pro (32/64 bit)
------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------



Processor	Intel Corei7 2.8 GHz or higher
Memory	2 GB or more
Web Browser	Microsoft Internet Explorer Ver. 7.0, Ver. 8.0, Ver. 9.0, Ver. 10.0, Ver. 11.0 Firefox Ver. 19.02 (plug-in free viewer only) Safari Ver. 5.1 (plug-in free viewer only) Google Chrome Ver. 25.0 (plug-in free viewer only)
SNC toolbox	Yes
SNC toolbox mobile	Yes

## Network

Protocols	IPv4, TCP, UDP, ARP, ICMP, IGMP*, HTTP, DHCP, DNS, NTP, RTP/RTCP, RTSP over TCP, SMTP over HTTP, IPv6, HTTPS, FTP (client), SNMP (v1, v2c, v3), SSL *SSM (Source Specific Multicast) is supported.
Number of IP Address/Mac ADDRESS	1

QoS	DSCP
Multicast Streaming Support	Yes
ONVIF Conformance	Profile S, Profile T
Authentication	IEEE802.1X

## Interface

Analog Monitor Output for Setup	Mini jack x1
Network Port	10BASE-T/100BASE-TX (RJ-45)

## General

Power Requirements	IEEE 802.3af compliant (PoE system)
Power Consumption	5.0 W max.
Operating Temperature	-10°C to +60°C 14°F to 140°F
Cold Start Temperature	0°C to +60°C 32°F to 140°F
Storage Temperature	-20 °C to + 60 °C -4 °F to + 140 °F

Operating Humidity	20 % to 80 %
Storage Humidity	20 % to 95 %
Dimensions *1	<p>72 mm x 63 mm x 145 mm (without lens)</p> <p>2 7/8 inches x 2 1/2 inches x 5 3/4 inches (without lens)</p> <p>72 mm x 63 mm x 199 mm (with lens)</p> <p>2 7/8 x 2 1/2 x 7 7/8 inches (with lens)</p>
Mass	<p>Approx. 505 g (with lens)</p> <p>Approx. 1 lb 1.8oz (with lens)</p>
External Material	<p>Top cover: SECC-CF</p> <p>Bottom cover: SECC-CF</p> <p>Front panel: ADC12</p> <p>Rear panel: PC + ABS</p>
External Color	<p>Top cover: Munsell 3.6GY 8.4/0.3</p> <p>Bottom cover: Munsell 3.6GY 8.4/0.3</p> <p>Front panel: Munsell 3.5PB 2.2/0.4</p> <p>Rear panel: Munsell 4.4BG 8.4/0.2</p>
Fire Retardant	UL2044
	<p>JATE Technical standard (LAN)</p> <p>UL2044, IEC60950-1 (CB)</p> <p>VCCI (Class A), FCC (Class A), IC</p>

Safety Regulations

(Class A)  
 Emission: EN55022 (Class A) + EN50130-4  
 Immunity: EN55022 (Class A) + EN55024  
 Emission: AS/NZS CISPR22 (Class A)  
 KCC  
 EMC-TR

Supplied Accessories

CD-ROM (supplied programs) (1)  
 Installation Manual (1)  
 Wire rope (1)  
 Screw (M4 × 8) (1)  
 Safety regulations (1)

## Notes

\*1 The values for dimensions are approximate.

## Related products



**SNC-UNI**



**SNC-UNIHB**

Outdoor fixed camera housing



**FWL-65W855C**

65" BRAVIA Professional Full HD Colour LED Display



**FWL-75W855C**

75" BRAVIA Professional Full HD Colour LED Display



## FWL-55W805C

55" BRAVIA Professional Full HD Colour LED Display



## FWL-40W705C

40" BRAVIA Professional Full HD Colour LED Display



## FWL-48W705C

48" BRAVIA Professional Full HD Colour LED Display



## SNCA-CEILING

Mounting coupling for pendant applications



## SNCA-POLE30

Mounting pipe for pendant mount applications



## SNCA-WMFX10PC

Wall/Ceiling camera bracket



## SNCA-WM40

Heavy duty outdoor wall mount for the SNC-RS84P, SNC-RS86P and SNC-RH164 rapid dome cameras



## UNI-WMB3

Wall mount bracket for PTZ dome mount security camera housings



## UNI-XBS1/T

Silver bracket for SNC-CH110S and SNC-CH210S



## UNI-OPL7C3

Outdoor Pressurized dome camera housing



## SNCA-HRX550/EXT

Robust, IP66 rated dome housing for Sony PTZ cameras



## UNI-OTBC6

Pressurized temperature controlled vandal-resistant security camera housing



## UNI-OTBC2

Temperature-controlled vandal-resistant outdoor security camera

housing

## Gallery

