

VPL-CX235

4,100 lumens XGA Basic Installation
projector



Overview

Feature-rich projector for budget conscious users

The VPL-CX235 offers great XGA 4:3 resolution and environmentally-friendly features for a low total cost of ownership. The VPL-CX235 incorporates Sony's BrightEra™ 3LCD inorganic panel technology that delivers higher picture quality, substantially brighter images, higher efficiency, better contrast, consistent colour stability and longer durability and usability.

MAXIMUM 4,100 LUMENS BRIGHTNESS

The VPL-CX235 features three brightness modes to suit individual user's needs – 4,100, 3,100 and 2,200 lumens. The low brightness mode generates lower operating costs by reducing power consumption and extending the recommended lamp replacement time to approximately 5,000 hours. The projector also has a contrast ratio of 3100:1, a range of video inputs, including HDMI, and RJ45 or RS-232C connectors for control.

Features

Maximum 4,100 lumens brightness with High, Standard and Low modes

The VPL-CX235 features three brightness modes for different uses – High 4,100 lumens for naturally white presentations in bright rooms, Standard 3,100 lumens for everyday use, and Low 2,200 lumens for video in darkened rooms.

1.66:1 to 2.41:1 throw ratio

The VPL-CX235 offers a 1.66:1 to 2.41:1 throw ratio that can accommodate most large classrooms or large meeting rooms.

3LCD BrightEra™ technology

Sony's 0.63-inch BrightEra 3LCD panels deliver improved panel light resistance, higher resolution, high brightness and increased panel reliability.

XGA 4:3 resolution

The VPL-CX235 has a native XGA (1024 x 768) 4:3 screen resolution panel that is perfect for presentations direct from video, laptop or PC.

5,000 hours recommended lamp replacement time

Extended lamp replacement time is possible with a new driving scheme that reduces gap expansion and brightness gradation, plus a new cooling system that allows uniformity in the temperature of the glass bulb and prevents it from clouding.

ECO Mode

Users can easily select power-saving ECO Mode. The most energy-efficient mode is accessible through a single button-push, and further adjustments are available through an easily understood menu system.

Lamp Dimming

With Lamp Dimming, the projector can reduce power consumption and brightness by 10-15% without user detection. After a pre-set time assigned by the user, the brightness and power consumption will reduce to 30% power usage. Instant 100% brightness returns with a new signal input to the projector.

Picture Mute

Picture Mute reduces power consumption down to 30% power usage, saving cost and lamp hours. This feature can be used in the education market as an instant off / on between class changes, or in the corporate market as a tool to redirect attention away from the screen and reduce power.

Vertical and horizontal keystone adjustment

The projector can correct keystone distortion by V: +/- 30% H: +/- 20% for perfect installation adjustment. (Note: Since this is an electronic correction, it will reduce the picture quality slightly).

Smart APA (Auto Pixel Alignment)

When a computer is used as a picture source, APA automatically optimises Phase, Pitch and Shift values. These can also be adjusted manually.

Auto Input Search

Auto Input Search detects which input has an incoming signal and automatically switches to it. This makes it easier for users to set up the projector prior to making a presentation.

Audio switcher facility

To avoid the need for a separate audio switcher, the projector can be used to select between two audio sources, routing them via a variable audio output to the room amplification system.

Picture Freeze function

Picture Freeze is useful during presentations if you need to look at other material on your PC's screen without the viewing audience being aware. Freeze the current image, and you can use your PC independently of the display from the projector.

Digital Zoom

With Digital Zoom, if you are displaying a computer-sourced image, you can enlarge a selected area of the screen image.

Off and Go

At the end of a presentation, you can turn off the power supply to the projector immediately, instead of going through a 'power down' cycle.

Direct Power On/Off

With this function, there is no need to go through Standby mode when powering up the projector. The projector can be set to activate as soon as power is applied.

Filter cleaning at the same time as lamp replacement

The filter only needs to be cleaned when a new lamp is fitted, potentially halving disruption due to maintenance.

Multiple Picture modes

The VPL-CX235 has six picture modes (Dynamic, Standard, Game, Living, Cinema and Presentation) that can be selected to suite the nature of the source material.

Built-in security measures

The VPL-CX235 has a package of security measures, including password protection, and physical anti-theft anchor points.

Display

Brightness - Modes High / Standard / Low	4100 / 3100 / 2200
Contrast	3 100:1
Native resolution	XGA (1024x768)
Panel size	0,63" BrightEra panles
Technology	3 x LCD

Optical

Autofocus	No
Keystone correction	V: +/- 30°, H: +/- 20°
Lens Shift	V: +5%, H: +/-4%
Optical Zoom	x1.5 (manual)
Screen size (diagonal)	40" to 300" (1.02m to 7.62m)
Throw ratio	1.66:1 to 2.41:1

Inputs

3D Sync	-
5 BNC	1
Components	1
Composite	1
DVI-D	1
Ethernet RJ45	Yes
HDMI	1
RS232C / CTRL S	1 / 1
Sub-D15	1
S-Video	1
USB File Viewer	-
Wireless LAN	-

Outputs

12V trigger	-
Audio Output	1
Direct power	-

Outputs

Monitor out	1
Off and Go	Yes
Speakers	-

Compatibility

Compatibility HDTV / DTV	Yes
Compatibility MAC / PC	Yes

General characteristics

Back adjustable feet	No
Cleaning filter	5000 hours
Dimensions - WxHxD mm	330,5 x 122,3 x 406
Lamp life - High / Medium / Low	3000 / 4000 / 5000 hours
Lamp reference	LMP-C240
Lamp type	245W
Speakers	1 x 10W Mono
Power Consumption (Standby Mode) - AC 100 V to 120 V	0.5W (when "Standby mode" is set to "Low")
Power Consumption (Standby Mode) - AC 220 V to 240 V	0.5W (when "Standby mode" is set to "Low")
Power Consumption (Networked Standby Mode) - AC 100 V to 120 V	3.0 W (LAN) (when "Standby Mode" is set to "Standard")
Power Consumption (Networked Standby Mode) - AC 220 V to 240 V	3.0 W (LAN) (when "Standby Mode" is set to "Standard")
Standby Mode/Network Standby Mode Activated	After about 10 minutes
Heat dissipation - AC 100 V to 120 V	1160 BTU
Heat dissipation - AC 220 V to 240 V	1092 BTU
Dimensions (W x H x D)	Approx. 406 x 113 x 330.5 mm (15 31/32 x 4 7/16 x 13 inches)
Mass	Approx. 5.5 kg (12 lb)

Environmental notice for customers in the USA

Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for additional information.

Gallery

