

CBK-DL1

USB Expansion Adapter for
Shoulder and Handheld
Camcorders



Overview

CBK-DL1 is a USB interface expansion adapter with DC 12V input / output terminal and can be powered by camcorder or other external source. It enables additional network functions by doubling the number of USB connectors on applicable cameras. Network features include Dual Link QoS Streaming*, FTP transfer** using Content Brower Mobile and more.

* To use cellular Dual Link functionality with XDCAM air, please contact your Sony sales representative to enquire about an optional license. In countries where XDCAM air is not available, it is possible to stream directly to on-premise network RX stations PWS-100RX1, PWS-110RX1, and PWS-110RX1A with an optional license activated.

** FTP transfer uses a single cellular connection.

Please note CBK-DL1 does not include cellular modem or USB wireless LAN module. A carrier use contract is necessary for data communication. For recommended cellular modems, please contact your Sony sales representative.

Recommended compatible camcorders include PXW-X500, PXW-X400, PXW-Z450, PXW-Z190 and PXW-Z280.

CBK-DL1 can be used with optional network adapter CBK-WA100 and CBK-WA101 that works with other Sony shoulder-mount products such as PMW-400, PXW-X320, PDW-850, PDW-700, PDW-F800, PDW-680, PMW-500, PMW-350, and PMW-320. CBK-DL1 is

supplied with a mounting bracket for shoulder-mount camcorders, and it is not required to purchase mounting accessories.

Handheld camcorders such as PXW-Z280, PXW-Z190 and PXW-X200 require 3rd party PROTECH mounting brackets to support the CBK-DL1. In addition, PXW-Z190 requires installation of an optional CBKZ-SLNW1 Network Licence key to enable networking functions.

Specifications

| General | |
|---|---|
| Supply voltage | 11 V to 17 V DC |
| Power consumption | Approx. 1.3 W |
| Operating temperature | 0 °C to 40 °C (32 °F to 104 °F) |
| Operating humidity | 20% to 90% |
| Storage temperature | -20 °C to +60 °C (-4 °F to 140 °F) |
| Dimensions (width / height / depth, excluding protrusions) | 96 × 133 × 48 mm (3 7/8 × 5 1/4 × 1 15/16 inches) |
| Mass Approx. | 180 g (6.3 oz) |
| Design and specifications are subject to change without notice. | |

Related products



CBK- WA100

Wireless adapter for Camcorders and Decks [Mobile network 3G / 4G / LTE /Wireless LAN]



CBK- WA101

Wireless adapter for PMW-400 and PXW-X320 [Mobile network 3G / 4G / LTE /Wireless LAN]



PWS- 110RX1A

Network RX Station

Gallery

